



# SAPPHIRE Hi-Pressure

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830  
Issue date: 10/11/2020 Revision date: 11/02/2021 Version: 7.1

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

Product form : Mixture  
Trade name : SAPPHIRE Hi-Pressure

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

##### 1.2.1. Relevant identified uses

Main use category : Industrial use, Professional use  
Industrial/Professional use spec : For professional use only  
Industrial  
Use of the substance/mixture : Lubricants, Greases and Release Products

##### 1.2.2. Uses advised against

No additional information available

#### 1.3. Details of the supplier of the safety data sheet

##### Manufacturer

ROCOL a division of ITW Ltd  
Rocol House  
Wakefield Rd, Swillington  
LS26 8BS Leeds - United Kingdom  
T +44 (0)113 232 2600  
[customer.service@rocol.com](mailto:customer.service@rocol.com) - [www.rocol.com](http://www.rocol.com)

#### 1.4. Emergency telephone number

Emergency number : +44 (0)113 232 2600

### SECTION 2: Hazards identification

#### 2.1. Classification of the substance or mixture

##### Classification according to Regulation (EC) No. 1272/2008 [CLP]

Oxidising solids Not classified  
Full text of H statements : see section 16

##### Adverse physicochemical, human health and environmental effects

No additional information available

#### 2.2. Label elements

##### Labelling according to Regulation (EC) No. 1272/2008 [CLP]

No labelling applicable

#### 2.3. Other hazards

No additional information available

### SECTION 3: Composition/information on ingredients

#### 3.1. Substances

Not applicable

# SAPPHIRE Hi-Pressure

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

### 3.2. Mixtures

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
Disodium sebacate	(CAS-No.) 17265-14-4 (EC-No.) 241-300-3 (REACH-no) 01-2120762063-61	1 – 2.4	Eye Irrit. 2, H319

Full text of H-statements: see section 16

## SECTION 4: First aid measures

### 4.1. Description of first aid measures

First-aid measures general	: Never give anything by mouth to an unconscious person. If you feel unwell, seek medical advice.
First-aid measures after inhalation	: Allow affected person to breathe fresh air. Allow the victim to rest.
First-aid measures after skin contact	: Remove affected clothing and wash all exposed skin area with mild soap and water, followed by warm water rinse.
First-aid measures after eye contact	: Rinse immediately with plenty of water. Obtain medical attention if pain, blinking or redness persists.
First-aid measures after ingestion	: Rinse mouth. Do NOT induce vomiting. Obtain emergency medical attention.

### 4.2. Most important symptoms and effects, both acute and delayed

Symptoms/effects	: Not expected to present a significant hazard under anticipated conditions of normal use.
------------------	--

### 4.3. Indication of any immediate medical attention and special treatment needed

No additional information available

## SECTION 5: Firefighting measures

### 5.1. Extinguishing media

Suitable extinguishing media	: Foam. Dry powder. Carbon dioxide. Water spray. Sand.
Unsuitable extinguishing media	: Do not use a heavy water stream.

### 5.2. Special hazards arising from the substance or mixture

No additional information available

### 5.3. Advice for firefighters

Firefighting instructions	: Use water spray or fog for cooling exposed containers. Exercise caution when fighting any chemical fire. Prevent fire fighting water from entering the environment.
Protection during firefighting	: Do not enter fire area without proper protective equipment, including respiratory protection.

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

#### 6.1.1. For non-emergency personnel

Emergency procedures	: Evacuate unnecessary personnel.
----------------------	-----------------------------------

#### 6.1.2. For emergency responders

Protective equipment	: Equip cleanup crew with proper protection.
Emergency procedures	: Ventilate area.

### 6.2. Environmental precautions

Prevent entry to sewers and public waters. Notify authorities if liquid enters sewers or public waters.

# SAPPHIRE Hi-Pressure

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

### 6.3. Methods and material for containment and cleaning up

Methods for cleaning up : On land, sweep or shovel into suitable containers. Minimise generation of dust.

### 6.4. Reference to other sections

See Heading 8. Exposure controls and personal protection.

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

Precautions for safe handling : Wash hands and other exposed areas with mild soap and water before eating, drinking or smoking and when leaving work. Provide adequate ventilation to minimize dust and/or vapour concentrations.

### 7.2. Conditions for safe storage, including any incompatibilities

Storage conditions : Keep container closed when not in use. Keep only in original container.  
Incompatible products : Strong bases. Strong acids.  
Incompatible materials : Sources of ignition. Direct sunlight.

### 7.3. Specific end use(s)

No additional information available

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

#### 8.1.1 National occupational exposure and biological limit values

No additional information available

#### 8.1.2. Recommended monitoring procedures

No additional information available

#### 8.1.3. Air contaminants formed

No additional information available

#### 8.1.4. DNEL and PNEC

No additional information available

#### 8.1.5. Control banding

No additional information available

### 8.2. Exposure controls

#### 8.2.1. Appropriate engineering controls

No additional information available

#### 8.2.2. Personal protection equipment

##### Personal protective equipment:

Avoid all unnecessary exposure.

##### 8.2.2.1. Eye and face protection

###### Eye protection:

Chemical goggles or safety glasses

##### 8.2.2.2. Skin protection

###### Hand protection:

Wear protective gloves. Nitrile rubber gloves

# SAPPHIRE Hi-Pressure

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

### 8.2.2.3. Respiratory protection

#### Respiratory protection:

Not required for normal conditions of use

### 8.2.2.4. Thermal hazards

No additional information available

### 8.2.3. Environmental exposure controls

#### Other information:

Do not eat, drink or smoke during use.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

Physical state	: Solid
Colour	: Blue-black.
Odour	: odourless.
Odour threshold	: No data available
pH	: No data available
Relative evaporation rate (butylacetate=1)	: No data available
Melting point	: No data available
Freezing point	: No data available
Boiling point	: No data available
Flash point	: > 200 °C
Auto-ignition temperature	: > 200 °C
Decomposition temperature	: No data available
Flammability (solid, gas)	: Non flammable.
Vapour pressure	: No data available
Relative vapour density at 20 °C	: No data available
Relative density	: ≈ 0.95
Solubility	: No data available
Partition coefficient n-octanol/water (Log Pow)	: No data available
Viscosity, kinematic	: No data available
Viscosity, dynamic	: No data available
Explosive properties	: No data available
Oxidising properties	: No data available
Explosive limits	: No data available

### 9.2. Other information

VOC content : 0 g/l

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

The product is non-reactive under normal conditions of use, storage and transport.

### 10.2. Chemical stability

Stable under normal conditions.

### 10.3. Possibility of hazardous reactions

Stable under normal conditions of use.

### 10.4. Conditions to avoid

Direct sunlight. Extremely high or low temperatures.

# SAPPHIRE Hi-Pressure

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

### 10.5. Incompatible materials

Strong acids. Strong bases.

### 10.6. Hazardous decomposition products

fume. Carbon monoxide. Carbon dioxide.

## SECTION 11: Toxicological information

### 11.1 Information on toxicological effects

Acute toxicity (oral) : Not classified  
Acute toxicity (dermal) : Not classified  
Acute toxicity (inhalation) : Not classified

#### Disodium sebacate (17265-14-4)

LD50 oral rat	> 5000 mg/kg
LD50 dermal rat	> 2000 mg/kg

Skin corrosion/irritation : Not classified  
Additional information : Based on available data, the classification criteria are not met  
Serious eye damage/irritation : Not classified  
Additional information : Based on available data, the classification criteria are not met  
Respiratory or skin sensitisation : Not classified  
Additional information : Based on available data, the classification criteria are not met  
Germ cell mutagenicity : Not classified  
Additional information : Based on available data, the classification criteria are not met  
Carcinogenicity : Not classified  
Additional information : Based on available data, the classification criteria are not met  
  
Reproductive toxicity : Not classified  
Additional information : Based on available data, the classification criteria are not met  
  
STOT-single exposure : Not classified  
Additional information : Based on available data, the classification criteria are not met  
  
STOT-repeated exposure : Not classified  
Additional information : Based on available data, the classification criteria are not met  
  
Aspiration hazard : Not classified  
Additional information : Based on available data, the classification criteria are not met  
  
Potential adverse human health effects and symptoms : Based on available data, the classification criteria are not met

## SECTION 12: Ecological information

### 12.1. Toxicity

Hazardous to the aquatic environment, short-term (acute) : Not classified  
Hazardous to the aquatic environment, long-term (chronic) : Not classified

### 12.2. Persistence and degradability

#### SAPPHIRE Hi-Pressure

Persistence and degradability	Not established.
-------------------------------	------------------

# SAPPHIRE Hi-Pressure

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

### 12.3. Bioaccumulative potential

#### SAPPHIRE Hi-Pressure

Bioaccumulative potential	Not established.
---------------------------	------------------

### 12.4. Mobility in soil

No additional information available

### 12.5. Results of PBT and vPvB assessment

No additional information available

### 12.6. Other adverse effects

Additional information : Avoid release to the environment.

## SECTION 13: Disposal considerations

### 13.1. Waste treatment methods

Product/Packaging disposal recommendations : Dispose in a safe manner in accordance with local/national regulations.  
Ecology - waste materials : Avoid release to the environment.

## SECTION 14: Transport information

In accordance with ADR / IMDG / IATA / ADN / RID

ADR	IMDG	IATA	ADN	RID
<b>14.1. UN number</b>				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
<b>14.2. UN proper shipping name</b>				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
<b>14.3. Transport hazard class(es)</b>				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
<b>14.4. Packing group</b>				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
<b>14.5. Environmental hazards</b>				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
No supplementary information available				

### 14.6. Special precautions for user

#### Overland transport

Not regulated

#### Transport by sea

Not regulated

#### Air transport

Not regulated

#### Inland waterway transport

Not regulated

#### Rail transport

Not regulated

### 14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable

# SAPPHIRE Hi-Pressure

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

### SECTION 15: Regulatory information

#### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

##### 15.1.1. EU-Regulations

Contains no REACH substances with Annex XVII restrictions

Contains no substance on the REACH candidate list

Contains no REACH Annex XIV substances

Contains no substance subject to Regulation (EU) No 649/2012 of the European Parliament and of the Council of 4 July 2012 concerning the export and import of hazardous chemicals.

Contains no substance subject to Regulation (EU) No 2019/1021 of the European Parliament and of the Council of 20 June 2019 on persistent organic pollutants

VOC content : 0 g/l

##### 15.1.2. National regulations

No additional information available

#### 15.2. Chemical safety assessment

No chemical safety assessment has been carried out

### SECTION 16: Other information

Data sources : REGULATION (EC) No 1272/2008 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006.

Other information : None.

Full text of H- and EUH-statements:	
Eye Irrit. 2	Serious eye damage/eye irritation, Category 2
H319	Causes serious eye irritation.

Safety Data Sheet (SDS), EU

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product.