

Product characteristics

Electronic pressure sensor

e1 compliant

Process connection: 1/4" NPT A / M5 I

Analogue output

Measuring range: 0...3000 psi

Application

Application

Type of pressure: relative pressure  
Liquids and gases

Use in gases at pressures > 363 psi (25 bar) only after contacting the manufacturer ifm

Pressure rating	[psi]	5800
-----------------	-------	------

Bursting pressure min.	[psi]	12300
------------------------	-------	-------

Medium temperature	[°C]	-25...90
--------------------	------	----------

Electrical data

Electrical design

DC

Operating voltage	[V]	9.6...32 DC
-------------------	-----	-------------

Insulation resistance	[MΩ]	> 100 (500 V DC)
-----------------------	------	------------------

Protection class		III
------------------	--	-----

Reverse polarity protection		yes
-----------------------------	--	-----

Outputs

Output		Analogue output
--------	--	-----------------

Output function		4...20 mA
-----------------	--	-----------

Overload protection		yes
---------------------	--	-----

Max. load	[Ω]	(Ub - 9.6 V) x 50; 720 at Ub = 24 V
-----------	-----	-------------------------------------

Measuring / setting range

Measuring range	[psi]	0...3000
-----------------	-------	----------

Accuracy / deviations

Accuracy / deviations  
(in % of the span)

Characteristics deviation *)		< ± 0.35 (BFSL) / < ± 0.75 (LS)
------------------------------	--	---------------------------------

Repeatability **)		< 0.15
-------------------	--	--------

Long-term stability ***)		< ± 0.05
--------------------------	--	----------

Temperature coefficients (TEMPCO) in the temperature range 0...80° C (in % of the span per 10 K)

Greatest TEMPCO of the zero point		0.2
-----------------------------------	--	-----

Greatest TEMPCO of the span		0.3
-----------------------------	--	-----

Reaction times

Step response time analogue output	[ms]	3
------------------------------------	------	---

# PX3111 - Electronic pressure sensor - eclass: 27201302 / 27-20-13-02

## Environment

Ambient temperature	[°C]	-25...80
Storage temperature	[°C]	-40...100
Protection		IP 68 / IP 69K

## Tests / approvals

EMC	EN 61000-4-2 ESD: EN 61000-4-3 HF radiated: EN 61000-4-4 Burst: EN 61000-4-6 HF conducted:  radiation of interference  noise immunity HF radiated  pulse resistance	4 kV CD / 8 kV AD 30 V/m 2 kV 10 V  according to the automotive directive 2004/104/EC / CISPR25  according to the automotive directive 2004/104/EC / ISO 11452-2 100 V/m  according to ISO7637-2 / severity level 3
Shock resistance	DIN IEC 68-2-27:	50 g (11 ms)
Vibration resistance	DIN IEC 68-2-6:	20 g (10...2000 Hz)


## Mechanical data

Process connection	1/4" NPT A / M5 I
Materials (wetted parts)	stainless steel (303S22); ceramics; FPM (Viton)
Housing materials	stainless steel 316L / 1.4404; FPM (Viton); PA; EPDM/X (Santoprene)
Min. pressure cycles	100 million
Weight [kg]	0.213

## Electrical connection

Connection	M12 connector; Gold-plated contacts
------------	-------------------------------------

## Wiring



## Remarks

Remarks	*) BFSL = Best Fit Straight Line / LS = Limit Value Setting **) with temperature fluctuations < 10 K ***) in % of value of measuring range / 6 months
Pack quantity [piece]	1

ifm electronic gmbh • Friedrichstraße 1 • 45128 Essen — We reserve the right to make technical alterations without prior notice. — GB — PX3111 — 22.01.2014