

RECHARGEABLE BUFFER BATTERY FOR MOBILE PANEL DP, CONNECTED WITH CABLES, MOBILE PANEL PN, CONNECTED WITH CABLES, MOBILE PANEL 277 IWLAN, MOBILE PANEL 277F IWLAN




Figure similar

Product type designation

Installation type/mounting

Wall mounting/direct mounting possible	Yes; in HMI devices, battery compartment
--	--

Supply voltage

Type of supply voltage	DC
Rated value (DC)	3.6 V; 1.15 Ah

Battery

Design

• Special design	Yes; Flat
------------------	-----------

Technology

• Lithium-ion	Yes; 1/CP7/34/50 01 CGA
---------------	-------------------------

Standards, approvals, certificates

CE mark	Yes
---------	-----

Ambient conditions

Ambient temperature in operation

• Min.	0 °C
• max.	55 °C

Storage/transport temperature

• Min.	-20 °C
• max.	70 °C

Relative humidity

• Operation, max.	90 %
-------------------	------

Dimensions	
Width	35 mm
Height	50 mm
Thickness	10 mm

Weights	
Without packaging	38 g

Scope of supply	
Delivery unit in items	1; incl. 65 mm connecting cable

other	
Note:	for Mobile Panel DP cabled, Mobile Panel PN cabled, Mobile Panel 277 IWLAN, Mobile Panel 277F IWLAN

Usable in the following products	
• Product 1	6AV6645-0AA01-0AX0
• Product 2	6AV6645-0AB01-0AX0
• Product 3	6AV6645-0AC01-0AX0
• Product 4	6AV6645-0BA01-0AX0
• Product 5	6AV6645-0BB01-0AX0
• Product 6	6AV6645-0BC01-0AX0
• Product 7	6AV6645-0DD01-0AX0
• Product 8	6AV6645-0DE01-0AX0
• Product 9	6AV6645-0DB01-0AX0

last modified: 12.03.2015