Connection Line M8 × 1; 3-pin



S56-5MPUR

Part Number




Technical Data

Mechanical Data		
	Coolect cooled	
Connection 1	Socket, angled	
Connection mode 1	M8 × 1, 3-pin	
Connection 2	stripped	
Torque	M8: 0,4 Nm	
Cable Length	5 m	
Cable Diameter	4,3 mm	
Wire cross-section	0,25 mm ²	
Display	LED	
Degree of Protection	IP67	
Temperature Range	-2580 °C	
Cable Jacket Material	PUR	
Material Wire Insulation	PP	
Material Sleeve Nut	CuZn, nickel-plated	
Halogen-free	yes	
Drag Chain Suitable	yes	
Bending radius (fixed installation)	5 × d	
Bending radius (used in motion)	10 × d	
Travel speed (with 5 m horizontal travel distance)	≤ 3,3 m/s	
Acceleration	≤ 5 m/s²	
Bending cycles	≤ 5000000	
Packaging unit	1 Piece	
Connection Diagram No.	S05	
Connection Equipment No.	8	

• Halogen free, drag chain suitability

• PUR, with LED, angled



Legen	d		PT	P
+	Supply Voltage +		пс	nc
-	Supply Voltage 0 V		U	Те
~	Supply Voltage (AC Voltage)		Ū	Te
A	Switching Output	(NO)	W	Tri
Ā	Switching Output	(NC)	W -	G
V	Contamination/Error Output	(NO)	0	Ar
V	Contamination/Error Output	(NC)	0-	G
E	Input (analog or digital)		BZ	В
Т	Teach Input		Awv	Va
Z	Time Delay (activation)		a	Va
s	Shielding		b	Va
RxD	Interface Receive Path		SY	Sy
TxD	Interface Send Path		SY-	Gi
RDY	Ready		E+	Re
GND	Ground		S+	Er
CL	Clock		÷	G
E/A	Output/Input programmable		SnR	S١
0	IO-Link		Rx+/-	- Et
PoE	Power over Ethernet		Tx+/-	Et
IN	Safety Input		Bus	In
OSSD	Safety Output		La	Er
Signal	Signal Output		Mag	M
BI_D+/-	- Ethernet Gigabit bidirect. data line (A-D)			In

ENorsez Encoder 0-pulse 0-0 (TTL)

EDM

Platinum measuring resistor	ENARS422	Encoder A/Ā (TTL)
not connected	ENBRS422	Encoder B/B (TTL)
Test Input	ENA	Encoder A
Test Input inverted	ENв	Encoder B
Trigger Input	Амін	Digital output MIN
Ground for the Trigger Input	Амах	Digital output MAX
Analog Output	Аок	Digital output OK
Ground for the Analog Output	SY In	Synchronization In
Block Discharge	SY OUT	Synchronization OUT
Valve Output	Out	Brightness output
Valve Control Output +	м	Maintenance
Valve Control Output 0 V	rsv	reserved
Synchronization	Wire Colors according to DIN IEC 757	
Ground for the Synchronization	BK	Black
Receiver-Line	BN	Brown
Emitter-Line	RD	Red
Grounding	OG	Orange
Switching Distance Reduction	YE	Yellow
Ethernet Receive Path	GN	Green
Ethernet Send Path	BU	Blue
Interfaces-Bus A(+)/B(-)	VT	Violet
Emitted Light disengageable	GY	Grey
Magnet activation	WH	White
Input confirmation	PK	Pink
Contactor Monitoring	GNYE	Green/Yellow

