


MSDS No. : 980.1075 DATE PREPARED: 22/ 06/ 2018

PRODUCT NAME: GREASE



NFPA HAZARD RATING

4 -- Extreme 3 -- Height 2 -- Moderate

1 -- Slight 0 - Insignificant

1 CHEMICAL PRODUCT AND COMPANY IDENTIFICATION

PRODUCT NAME: Grease

PRODUCT CODE: 980.1075

COMPANY NAME: KS Tools Werkzeug-Maschinen GmbH, Seligenstädter Grund 10 -12,

D-63150 Heusenstamm, +49-6104-4974-0, kstools@kstools.de, www.kstools.de

DE, AUT, CHE, LUX (24h): Tel: ++49 69 222 25285 (Deutsch, **EMERGENCY TELEPHONE NUMBER:**

Englisch) Numéro d'appel d'urgence en cas d'intoxication/d'accident - Suisse, Luxembourg (24h): Tel: ++33 1 7211 0003 (Français)

COMPOSITION / INFORMATION ON INGREDIENTS

CHEMICAL FAMILY: Lubricating Grease. not applicable FORMULA

COMPONENTS:

CONTENTS (%) NAME Base oil (Refined mineral oil) 75 - 85Thickener (Lithium soap) 5 - 15EP additives (Containing molybdenum compound, zinc compound) <10 Additives <5

HAZARDOUS INGREDIENTS

CAS No. NAME CONTENTS (%) 1317-33-5 Molybdenum compound 1 - 3

See Section 8 for exposure limits (if applicable)

HAZARDOUS IDENTIFICATION

CLASS NAME OF HAZARDOUS CHEMICALS FOR SDS IN JAPAN Not applicable

· PHYSICAL AND CHEMICAL HAZARDS : Combustible

· ADVERSE HUMAN HEALTH EFFCTS: Prolonged and repeated contact may cause skin irritation.

• ENVIRONMENTAL EFFECTS: No data available.



MSDS No. : 980.1075 DATE PREPARED: 22/ 06 / 2018

PRODUCT NAME: MOLYLEX SPECIAL

4 FIRST AID MEASURES

EYES : Immediately flush with water for at least 15 minutes. Get medical attention if eye

irritation persists.

SKIN : Remove excess with cloth or paper and wash area thoroughly with soap and water.

INGESTION: Consult a physician. Do not induce vomiting.

<u>INHALATION</u>: Keep the victim warm and quiet. Remove the victim from the contamination Immediately to fresh air.

NOTE TO PHYSICIANS: Supportive care. Treatment based on judgment of the physician in response to reactions of the patient.

5 FIRE FIGHTING MEASURES

FLAMMABLE PROPERTIES:

• FLASH POINT: 205 METHOD: Seta Flash Method

• FLAMMABLE LIMITS: LFL: N/A UFL: N/A

AUTOIGNITION TEMPERATURE : no data available

• HAZARDOUS DECOMPOSITION PRODUCTS: Thermal decomposition and combustion may produce carbon monoxide and/or carbon dioxide.

* N/A: Not applicable.

EXTINGUISH MEDIA: Dry chemical, Water fog, CO 2, Foam, Sand/Earth

<u>FIRE FIGHTING INSTRUCTIONS</u>: Dense smoke. Fire fighter wear an approved self-contained breathing apparatus. Do not use water except fog.

6 ACCIDENTAL RELEASE MEASURES

<u>PROCEDURE FOR CLEAN-UP</u>: Transfer bulk of mixture into another container. Absorb residue with an inert material such as earth, sand and vermiculite.

Sweep up and dispose solid waste in accordance with local, state and federal regulations.

<u>WASTE DISPOSAL</u>: Dispose of in accordance with all applicable federal, state and local regulations.

7 HANDLING AND STORAGE

<u>HANDLING</u>: Contact with eye may cause irritation. Use protective glasses or other devices to avoid contact with eyes. Contact with skin may cause irritation. Use protective gloves to avoid skin contact.

Do not swallow. (Eating product cause diarrhea and vomiting.)

Wear gloves to avoid injury on hands at opening the container.

Keep out reach of children.

<u>STORAGE</u>: Keep container closed until ready for use. Storage away from fire source or sunlight and in cool dry area.



MSDS No. : 980.1075 DATE PREPARED: 22/ 06 / 2018

PRODUCT NAME: MOLYLEX SPECIAL

8 EXPOSURE CONTROLS / PERSONAL PROTECTION

CONTROL PARAMETERS:

Oil mist, mineral: ACGIH TLV (1999): TWA 5mg/m³

Molybdenum compound: ACGIH TLV (1999): TWA as Mo 10mg/m³

ENGINEERING MEASURES: none

PERSONAL PROTECTIVE EQUIPMENT:

- · RESPIRETORY PROTECTION: Good general ventilation should be sufficient for most condition.
- EYE PROTECTION: Chemical safety goggles and if handled hot, full face shield.
- · HAND AND BODY PROTECTION: Protective gloves, rubber or plastic oil resistant.
- · OTHER PROTECTIVE EQUIPMENT: none

9 PHYSICAL AND CHEMICAL PROPERTIES

• APPEARANCE : Grayish black paste • ODOR : Slight odor.

VAPOR DENSITY(AIR=1) :

(n-Butyl Acetate=1)

N/A

VAPOR PRESSURE N/A

SPECIFIC GRAVITY(H 2 O=1): 0.93

SOLUBILITY IN WATER Negligible
 EVAPORATION RATE Slower

· SOLUBILITY IN ---- : N/A

PH
BOILING POINT
N/A
FREEZING POINT
N/A
VISCOSITY
N/A

• MELTING POINT(Dropping Point): 205

* N/A: Not applicable.

1 0 STABILITY AND REACTIVITY

- STABILITY: (CONDITION TO AVOID) Product is stable under normal condition. Avoid over heating.
- INCOMPATIBILITY: (SPECIFIC MATERIALS TO AVOID) Strong oxidizers such as hydrogen peroxide, bromine, and chromic acid.
- HAZARDOUS DECOMPOSITION PRODUCTS: Oxide of lithium, sulfur, molybdenum, zinc, phosphorus.

HAZARDOUS POLYMERIZATION : noneREACTIVTY WITH WATER : none

1 1 TOXICOLOGICAL INFORMATION

- · CORROSIVE AND IRRITANT PROPERTIES: No data available
- · ALLERGENIC AND SENSITIZING EFFECTS :No data available
- ACUTE TOXICITY: Refined mineral oil LD50 Acute oral 5<g/kg(rat)
- SUB-CHRONIC TOXICITY: No data available
- · CHRONIC TOXICITY: Prolonged and repeated skin contact may cause irritation.
- CARCINOGENIC EFFECT:
 Not listed IARC,NTP,ACGIH.
- MUTAGENIC EFFECTS : No data available
- · EFFECTS ON THE REPRODUCTIVE SYSTEM: No data available
- TERATOGENIC EFFECTS:
 No data available



MSDS No. : 980.1075 DATE PREPARED: 22/ 06 / 2018

PRODUCT NAME: MOLYLEX SPECIAL

1 2 ECOLOGICAL INFORMATION

BIODEGRABILITY: No data available
 BIOACCUMULATION: No data available
 FISH TOXICITY: No data available

1 3 DISPOSAL CONSIDERATION

WASTE DISPOSAL METHOD: Incinerate in accordance with applicable regulation.

<u>ATTENTION</u>: Do not use pressure to empty this container. When empty, container may have vapor or product residue. Do not cut, puncture or weld on near the drum.

1 4 TRANSPORT INFORMATION

DOT : Not applicable UN No. : Not applicable

FIRE SERVICE LAW (JAPAN): Not applicable

1 5 REGULATORY INFORMATION

Regulatory information with regard to this product in your country or your region should be examined by your own responsibility.

US TSCA (Toxic Substances Control Act):

All components of this product are listed on the TSCA inventory of Chemical Substances.

US OSHA (Occupational Safety and Health Act):

This product is hazardous according to the OSHA Hazard Communication Standard, 29 CFR 1910.1200, since this product contains OSHA Hazardous Substances; Molybdenum compound.

US CERCLA (Comprehensive Environmental Release, Compensation & Liability Act):

Zinc compounds (0.5 - 1%) no RQ is assigned to this generic or broad class.

US SARA (Superfund Amendment & Reauthorization Act) Title

This product contains no Extremely Hazardous Substances.

SARA Hazard Categories (311/312): None

SARA Toxic Release Inventory (TRI) (313): Zinc compounds (0.5 – 1%)



MSDS No. : 980.1075 DATE PREPARED: 22/ 06 / 2018

PRODUCT NAME: MOLYLEX SPECIAL

1 6 OTHER INFORMATION

INFORMATION CONTACT KYODO YUSHI ASIA PT LTD

NO.2 GUL CRESCENT SINGAPORE 629518

Tel +65 6861 7737

REFERENCE: CMA Interim Guideline for the Preparation of MSDS.

Chapter 7: MSDS Examples.

ACGIH Threshold Limit Values for Chemical Substances in the Work Environment.

(1998-1999)

ORIGINAL DATE: 06 / 01 / 2000, REVISION DATE: 03 / 09 / 2004

This MSDS is an addition and complementary document beside the technical data sheet. The information is based upon our knowledge about the product at the date of edition. Since we cannot anticipate or control the different conditions under which these information or our product may be used, we make no guarantee that recommendations will be adequate for all individuals and situations.