

Fair-Rite Products Corp. PO Box J,One Commercial Row, Wallkill, NY 12589-0288 Phone: (888) 324-7748 www.fair-rite.com


Fair-Rite Product's Catalog Part Data Sheet, 2643166651 Printed: 2008-04-29











Part Number: 2643166651

Frequency Range: Broadband Frequencies 25-300 MHz (43 material)

Description: 43 SPLIT FLAT CABLE CORE

Application: Suppression Components

Where Used: Cable Component

Part Type: Flat Cable EMI Suppression Cores

Preferred Part:

Mechanical Specifications

Weight: 36.000 (g)

Part Type Information

Flat cable suppression core can accommodate multi-conductors flat cables, in widths from 12.7 mm (.500") up to 78 mm (3.1"). These flat cable cores are available in three ferrite material grades to reduce conducted EMI from 1 MHz into the GHz region.

- -Flat cable suppression cores, split or single cores, are controlled for impedances only. The impedances listed are typical values.

 Minimum impedance values are specified for the + marked frequencies. The minimum guaranteed impedance is the listed impedance less 20%.
- -Centered, single turn impedance tests for the 31 and 43 material are made on the 4193A Vector Impedance Analyzer. All tests are made with the shortest practical wire length.
- -Assembly clips are available for most of the split flat cable cores. See section 'Flat Cable Core Assembly clips' in our catalog.
- -Our 'Expanded Cable & Suppressor Kit' (part number 0199000005) contains a selection of these flat cable cores and clips.
- -Explanation of Part Numbers: Digits 1 & 2 = product class and 3& 4 = material grade.



Fair-Rite Products Corp. PO Box J.One Commercial Row, Wallkill, NY 12589-0288 Phone: (888) 324-7748 www.fair-rite.com

Fair-Rite Product's Catalog Part Data Sheet, 2643166651 Printed: 2008-04-29









Mechanical Specifications

Dim	mm	mm	nominal	inch
		tol	inch	misc.
А	45.10	±0.75	1.775	-
В	34.40	±0.70	1.355	-
С	28.60	±0.70	1.125	-
D	6.35	±0.25	0.250	-
Е	0.85	±0.20	0.033	-
F	-	ı	-	-
G	-	ı	-	-
Н	-		-	-
J	-		-	-
K	-	-	-	-

Electrical Specifications

Typical Impedance (Ω)		
10 MHz	60	
25 MHz+	110	
100 MHz+	290	
250 MHz	435	

Electrical Properties	

Land Patterns

V	W	Х	Υ	Z
-	-	-		-

Winding Information

Turns	Wire	1st Wire	2nd Wire
Tested	Size	Length	Length
-	-	-	-

Reel Information

Tape Width	Pitch	Parts 7 "	Parts 13 "	Parts 14 "
mm	mm	Reel	Reel	Reel
-	-	-	-	-

Package Size

Pkg Size
-
(-)

Connector Plate

# Holes	# Rows
-	-

Legend

+ Test frequency

Preferred parts, the suggested choice for new designs, have shorter lead times and are more readily available.

The column H(Oe) gives for each bead the calculated dc bias field in oersted for 1 turn and 1 ampere direct current. The actual dc H field in the application is this value of H times the actual NI (ampere-turn) product. For the effect of the dc bias on the impedance of the bead material, see figures 18-23 in the application note How to choose Ferrite Components for EMI Suppression.

A ½ turn is defined as a single pass through a hole.

∠I/A - Core Constant

 A_e : Effective Cross-Sectional Area A_I - Inductance Factor $\binom{L}{N2}$

I e: Effective Path Length

Ve: Effective Core Volume

NI - Value of dc Ampere-turns

N/AWG - Number of Turns/Wire Size for Test Coil



Fair-Rite Product's Catalog Part Data Sheet, 2643166651 Printed: 2008-04-29









Ferrite Material Constants

Specific Heat 0.25 cal/g/°C

Thermal Conductivity 10x10⁻³ cal/sec/cm/°C

Coefficient of Linear Expansion 8 - 10x10⁻⁶/°C

Tensile Strength 4.9 kgf/mm²

Compressive Strength 42 kgf/mm²

Young's Modulus 15x10³ kgf/mm²

Specific Gravity $\approx 4.7 \text{ g/cm}^3$

The above quoted properties are typical for Fair-Rite MnZn and NiZn ferrites.

See next page for further material specifications.



Fair-Rite Products Corp. PO Box J,One Commercial Row, Wallkill, NY 12589-0288 Phone: (888) 324-7748 www.fair-rite.com

This NiZn is our most popular ferrite for suppression of conducted EMI from 20 MHz to 250 MHz. This material is also used for inductive applications such as high frequency common-mode chokes.

EMI suppression beads, beads on leads, SM beads, multi-aperture cores, round cable EMI suppression cores, round cable snap-its, flat cable EMI suppression cores, flat cable snap-its, miscellaneous suppression cores, bobbins, and toroids are all available in 43 material.

Fair-Rite Product's Catalog Part Data Sheet, 2643166651

Printed: 2008-04-29










43 Material Specifications:


Property	Unit	Symbol	Value
Initial Permeability ® B < 10 gauss		μ_{i}	800
Flux Density	gauss	В	2900
@ Field Strength	oersted	н	10
Residual Flux Density	gauss	B _r	1300
Coercive Force	oersted	H _o	0.45
Loss Factor	10-6	tan δ/μ;	250
@ Frequency	MHz		1.0
Temperature Coefficient of Initial Permeability (20 -70°C)	%/°C		1.25
Curie Temperature	°C	T _c	>130
Resistivity	Ωcm	ρ	1x10 ⁵

Complex Permeability vs. Frequency




Measured on a 17/10/6mm toroid using the HP 4284A and the HP 4291A.

Initial Permeability vs. Temperature




Measured on a 17/10/6mm toroid at 100kHz.

Percent of Original Impedance vs. Temperature



Measured on a 2643000301 using the HP4291A.

Hysteresis Loop



Measured on a 17/10/6mm toroid at 10kHz.



Fair-Rite Products Corp. PO Box J.One Commercial Row, Wallkill, NY 12589-0288 Phone: (888) 324-7748 www.fair-rite.com


Fair-Rite Product's Catalog Part Data Sheet, 2643166651 Printed: 2008-04-29











Impedance, reactance, and resistance vs. frequency.