

RANA Linear Surface&Suspended - Louvre+Prismatic Optic


RANA LINEAR S 3KLM NW LOUV+PRI D EMPRO

0051271



Product features

- Surface or Suspended LED Linear luminaire with Louvre + Micro Prismatic Optic, Dimensions: 1150mm x 87mm x 87mm, Direct, White Body, DALI Dimmable (Switch-Dim), Emergency 3 hours maintained, Neutral White LED (4000K), 3160lm, 31W, 102lm/W efficacy, CRI>80, 3 SDCM (3-step MacAdam ellipse), Low LED Flicker (+/-5%), UGR<19, L90B10 at 50,000 hours, Electric Class1, Glow Wire Test 850°C



PRODUCT OVERVIEW

Product name	RANA LINEAR S 3KLM NW LOUV+PRI D EMPRO
Technology	LED
Cap/Base	N/A
Housing	Steel
Mount	Ceiling surface mounting, Suspended
Fixture rating	Enclosed
Environment	Internal
General application	Office, Hospitality, Retail, Education
ETIM Class	EC002892
Warranty	5 years
Fixture luminous flux (lm)	3160
Luminaire efficacy (lm/W)	101.93
LOR (%)	100
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	80
Colour Consistency (SDCM)	3
Glare control	< 19
Photobiological Risk Group	RG0
Luminous flux (emergency) (lm)	531
Total power consumption (W)	31
Electrical protection	Class I
Control gear type	Electronic ballast
Dimmable	Yes
Dimming method	DALI
Minimum dimming level (%)	1
Housing colour	RAL 9016 - Traffic white / Bezel
IP rating	IP20
IK rating	IK07
Product EAN number	5410288512716

RANA Linear Surface&Suspended - Louvre+Prismatic Optic

RANA LINEAR S 3KLM NW LOUV+PRI D EMPRO
0051271

DATA TABLE

General data

Product name	RANA LINEAR S 3KLM NW LOUV+PRI D EMPRO
Technology	LED
Cap/Base	N/A
Housing	Steel
Mount	Ceiling surface mounting, Suspended
Fixture rating	Enclosed
Environment	Internal
General application	Office, Hospitality, Retail, Education
Operating temperature range (°C)	5°C...+30°C
Performance ambient temperature Tq (°C)	25
ETIM Class	EC002892
Warranty	5 years

Optical data

Fixture luminous flux (lm)	3160
Luminaire efficacy (lm/W)	101.93
LOR (%)	100
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	80
Colour Consistency (SDCM)	3
Adjustable chromaticity	N
Glare control	< 19
Photobiological Risk Group	RG0
Luminous flux (emergency) (lm)	531
Emergency duration (h)	3.0

Electrical data

Total power consumption (W)	31
Mains voltage (V)	220-240V
Electrical protection	Class I
Control gear type	Electronic ballast
Transformer required	Yes
Dimmable	Yes
Dimming method	DALI
Minimum dimming level (%)	1
Drive current (mA)	275
Inrush Current (A)	10
Inrush Duration (µs)	300
Glow Wire Test (°C)	850
Energy Efficiency Class (A->G) of contained light source	C
Nominal Frequency (Hz)	50/60Hz
Max. Luminaires per 16A C Breaker	22

RANA Linear Surface&Suspended - Louvre+Prismatic Optic

RANA LINEAR S 3KLM NW LOUV+PRI D EMPRO
0051271

Lifetime data

Lifespan L70 B50	60000
Lifespan L70 B20	60000
Lifespan L70 B10	60000
Lifespan L80 B50	60000
Lifespan L80 B20	60000
Lifespan L80 B10	60000
Lifespan L90 B50	60000
Lifespan L90 B20	60000
Lifespan L90 B10	60000

Physical data

Housing colour	RAL 9016 - Traffic white / Bezel
IP rating	IP20
IK rating	IK07
Diffuser finish	Prismatic
Diffuser material	PC Polycarbonate
Reflector finish	Matt
Nominal Product Length (mm)	1150
Nominal Product Width (mm)	87
Nominal Product Height (mm)	87
Weight (kg)	3.55

Packaging


Single packaging type	Carton
Product EAN number	5410288512716
Packaging single length / height (cm)	116.5
Packaging single width (cm)	10.5
Packaging single depth (cm)	10.0
DUN14 (outer)	05410288512716
Units per outer package	1
Packaging outer length / height (cm)	116.5
Packaging outer width (cm)	10.5
Packaging outer depth (cm)	10.0

Safety data

Optimal operating condition (°C)	5-30
----------------------------------	------


PHOTOMETRY

RANA Linear Surface & Suspended - Louvre + Prismatic Optic *RANA LINEAR S 3KLM NW LOUV+PRI D EMPRO* 0051271



Distance [m]	Cone diameter [m]	E(0°)	E(C90)	E(C0)	Illuminance [lx]
0.5	0.91 0.64	1488	42.2° 301	32.7° 439	
1.0	1.81 1.28	366	42.2° 76	32.7° 110	
1.5	2.72 1.93	163	42.2° 33	32.7° 49	
2.0	3.63 2.57	90	42.2° 19	32.7° 27	
2.5	4.53 3.21	59	42.2° 12	32.7° 18	
3.0	5.44 3.85	41	42.2° 8	32.7° 12	

Distance [m] Cone diameter [m] Illuminance [lx]
 — C0 - C180 (Half beam angle: 65.4°)
 — C90 - C270 (Half beam angle: 64.4°)



Distance [m]	Cone diameter [m]	E(0°)	E(C90)	E(C0)	Illuminance [lx]
0.5	0.95 0.66	794	43.8° 153	33.5° 234	
1.0	1.90 1.32	199	43.8° 38	33.5° 58	
1.5	2.85 1.99	88	43.8° 17	33.5° 26	
2.0	3.81 2.65	50	43.8° 9	33.5° 14	
2.5	4.76 3.31	32	43.8° 6	33.5° 9	
3.0	5.71 3.97	22	43.8° 4	33.5° 6	

Distance [m] Cone diameter [m] Illuminance [lx]
 — C0 - C180 (Half beam angle: 67.2°)
 — C90 - C270 (Half beam angle: 67.2°)

TECHNICAL DRAWINGS

