

Cutter for circular cutter, type 422

Application:

For use in a circular cutter, type 00 and 00a, with drawing cut for sheet metal, steel and non-ferrous metals with a max. cutting depth of 5 mm.



Art. no.	11370 141
Brand	GFS
Manufacturer Part Number	22 011 122
Form	422
Suitable for type	00, 00 a
Cutting material	HSSE
Surface	Uncoated
Gross Weight	0.010 kg
Product Group	119