

## Felt polishing and grinding points

Shank diameter 6 mm



### Application:

For pre-polishing and gloss polishing of injection moulding tools, fittings, cemented carbide cutting knives and for gloss polishing of stainless steel components (INOX).

### Advantage:

- Exact preservation of geometric shapes due to its hardness
- Freely profilable and can therefore also be used for tools with complicated geometries
- Exact preservation of geometric shapes due to its hardness



<b>Art. no.</b>	<b>69202 005</b>
<b>Brand</b>	PFERD
<b>Manufacturer Part Number</b>	4007220153772
<b>Form</b>	Cylindrical
<b>Head diameter x head length</b>	10 x 14 mm
<b>Min./max. recommended rotation speed</b>	10000-20000 rpm
<b>Max. rotation speed</b>	61000 rpm
<b>Number of pieces per packet</b>	10 PCS
<b>Gross Weight</b>	0.009 kg
<b>Product Group</b>	6AB

### EAN

4007220153772