

Pneumatic belt sander GB 815 H

MANNESMANN
DEMAG

Version:


- Powerful motor
- With telescopic belt tension
- Sanding belts of 8 and 15 mm can be used
- Exhaust air: rear

Advantage:

- Easy belt change
- Compact design - low weight

Delivery:

Grinding arm 15mm, hose unit



| | |
|--------------------------------|------------------|
| Art. no. | 75061 150 |
| Model | GB 815 H |
| Valve design | Lever valve |
| Max. belt speed | 20 m/s |
| Max. idle speed | 20000 rpm |
| Power input | 300 W |
| Air consumption | 10 l/s |
| Connection thread | G 1/4 inch |
| Length | 295 mm |
| Min. sanding belt width | 8 mm |
| Max. sanding belt width | 15 mm |
| Weight | 0.95 kg |
| Grinding belt length | 330 mm |

EAN-Code

425175730085 1

