

Pneumatic belt sander GB 815 H

**MANNESMANN
DEMAG**

Execution:


- Powerful motor
- With telescopic belt tension
- Sanding belts of 8 and 15 mm can be used
- Exhaust air: rear

Advantage:

- Easy belt change
- Compact design - low weight

Delivery:

Grinding arm 15mm, hose unit



Art. no.	75061 150
Brand	MANNESMANN DEMAG
Manufacturer Part Number	60010685
Model	GB 815 H
Valve design	Lever valve
Max. belt speed	20 m/s
Max. idle speed	20000 rpm
Power input	300 W
Air consumption	10 l/s
Connection thread	G 1/4 inch
Length	295 mm
Min. sanding belt width	8 mm
Max. sanding belt width	15 mm
Weight	0.95 kg
Grinding belt length	330 mm
Gross Weight	0.950 kg
Product Group	7AA

EAN

4251757300851

