3.2x1.6mm SMD CHIP LED LAMP

Part Number: KPTR-3216SURCK Hyper Red


Features

- 3.2mmx1.6mm SMT LED,1.05mm thickness.
- Low power consumption.
- Wide viewing angle.
- Ideal for backlight and indicator.
- Package : 2000pcs / reel.
- Moisture sensitivity level : level 3.
- RoHS compliant.

Description

The Hyper Red source color devices are made with Al-GalnP on GaAs substrate Light Emitting Diode.

Package Dimensions



SPEC NO: DSAA9356 APPROVED: Wynec REV NO: V.14A CHECKED: Allen Liu DATE: JUL/01/2015 DRAWN: F.T.Liu PAGE: 1 OF 5 ERP: 1203002425

Selection Guide

Selection Guide					
Part No.	Emitting Color (Material)	nitting Color (Material) Lens Type @ 20mA			Viewing Angle [1]
			Min.	Тур.	201/2
KPTR-3216SURCK	Hyper Red (AlGaInP)	Water Clear	120	230	120°
			*40	*80	

Notes:

1. 01 / 2 is the angle from optical centerline where the luminous intensity is 1 / 2 of the optical peak value.
2. Luminous intensity / luminous Flux: + / -15%.
* Luminous intensity value is traceable to the CIE127-2007 compliant national standards.

Electrical / Optical Characteristics at TA=25°C

Symbol	Parameter	Emitting Color	Тур.	Max.	Units	Test Conditions
λpeak	Peak Wavelength	Hyper Red	645		nm	I⊧=20mA
λD [1]	Dominant Wavelength	Hyper Red	630		nm	I⊧=20mA
Δλ1/2	Spectral Line Half-width	Hyper Red	28		nm	I⊧=20mA
С	Capacitance	Hyper Red	35		pF	VF=0V;f=1MHz
Vf [2]	Forward Voltage	Hyper Red	1.95	2.5	V	I⊧=20mA
lr	Reverse Current	Hyper Red		10	uA	VR=5V


Notes: 1. Wavelength: + / -1nm. 2. Forward Voltage: + / -0.1V. 3. Wavelength value is traceable to the CIE127-2007 compliant national standards.

Excess driving current and / or operating temperature higher than recommended conditions may result in severe light degradation or premature failure.

Absolute Maximum Ratings at TA=25°C


Parameter	Values	Units		
Power dissipation	75	mW		
DC Forward Current	30	mA		
Peak Forward Current [1]	185	mA		
Reverse Voltage	5	V		
Operating Temperature	-40°C To +85°C			
Storage Temperature	-40°C To +85°C			

Note: 1. 1 / 10 Duty Cycle, 0.1ms Pulse Width.



KPTR-3216SURCK

Reflow soldering is recommended and the soldering profile is shown below. Other soldering methods are not recommended as they might cause damage to the product.




APPROVED: Wynec

CHECKED: Allen Liu

DRAWN: F.T.Liu

PAGE: 4 OF 5 ERP: 1203002425



A The information is helded in this descent of the account of the second second is interested at

- 1. The information included in this document reflects representative usage scenarios and is intended for technical reference only.
- 2. The part number, type, and specifications mentioned in this document are subject to future change and improvement without notice. Before production usage customer should refer to the latest datasheet for the updated specifications.
- 3. When using the products referenced in this document, please make sure the product is being operated within the environmental and electrical limits specified in the datasheet. If customer usage exceeds the specified limits, Kingbright will not be responsible for any subsequent issues.
- 4. The information in this document applies to typical usage in consumer electronics applications. If customer's application has special reliability requirements or have life-threatening liabilities, such as automotive or medical usage, please consult with Kingbright representative for further assistance.
- 5. The contents and information of this document may not be reproduced or re-transmitted without permission by Kingbright.
- 6. All design applications should refer to Kingbright application notes available at http://www.kingbright.com/application_notes

DATE: JUL/01/2015 DRAWN: F.T.Liu