



FOR F-CM CONTACT MULTIPLIER CAN BE CODED  
FOR TRIPPING GROUP SG1 TO SG6 30MM

### General technical data:

<b>Product designation</b>		Terminal module
<b>Product type designation</b>		TM-FCM30 S47-E0 for F-CM
<b>Design of the product</b>		for F-CM modules
<b>Mounting height</b>	mm	196.5
<b>Installation width</b>	mm	30
<b>Installation depth</b>	mm	102
<b>Protection class IP</b>		IP20
<b>Insulation voltage Rated value</b>	V	500
<b>Operating voltage</b>		
• for DC Rated value	V	24
<b>Operating current Rated value</b>	A	10
<b>Type of connectable conductor cross-section</b>		
• solid		1x (0.14 ... 2.5 mm <sup>2</sup> )
• finely stranded with core end processing		1x (0.14 ... 1.5 mm <sup>2</sup> ), acc. to IEC 60947
• for AWG conductors		
— solid		1x (18 ... 22)
— stranded		1x (18 ... 22)

### Installation/ mounting/ dimensions:

<b>Size of the screwdriver tip</b>		Standard screwdriver Size 1
Tightening torque with screw-type terminals	N·m	0.4 ... 0.7

### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/industrial-controls/catalogs>

**Industry Mall (Online ordering system)**

<http://www.siemens.com/industrymall>

**Cax online generator**

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RK19033AB10>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<http://support.automation.siemens.com/WW/view/en/3RK19033AB10/all>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

<http://www.automation.siemens.com/bilddb/index.aspx?attID9=3RK19033AB10&lang=en>

last modified:

15.01.2015