## Powerpole® Connectors - PP120: up to 240 Amps



PP120 series Powerpole® housings are designed to accommodate up to 1/0 (50 mm²) wires and handle high currents up to 240 amps. Reducing bushings allow PP120 to accept down to #8 (10 mm²) wires. Multiple colors of stackable housings combine with low resistance flat wiping technology to offer powerful connection capability.


- Large Wire Range Accommodates up to 1/0 (50mm²) Wire Reducing bushings allow as small as #8 (10 mm²) wire to be used
- Low Resistance Silver Plated Copper Contacts
  Allows currents up to 240 amps
- UL Rated for Hot Plugging up to 60 Amps
   Great for battery or other applications where the ability to interrupt circuits is required

#### | PP120 ORDERING INFORMATION |

#### **PP120 Housings**

The second to largest Powerpole® housing can be used with wire contacts for up to 1/0 AWG [50mm²] or busbar contacts.


Description	Part Nu	ımbers
Minimum Quantity	. 500	50
Red	1321G3-BK	1321G3
Green	1321G4-BK	1321G4
Black	1321G1-BK	1321G1
White	1321G2-BK	1321G2
Blue	1321-BK	1321
Gray	1321G8-BK	1321G8



#### **PP120 Silver Plated Wire Contacts**

Silver plated contacts offer superior electrical performance and durability up to 10,000 mating cycles. New contacts for #1 to 1/0 AWG (35 to 50 mm²) offer extended capability in the same housings. See reducing bushings in accessory section for smaller wires.

		Mating				- A		- E	3 -
AWG	mm²	Force	Loose	Piece Part N	umbers	inches	mm	inches	mm
Minin	num Qua	antity	. 600	500	50				
1/0	53.5	Low	1323G2-BK	-	1323G2	0.52	13.21	0.44	11.18
1	42.4	Low	1323G1-BK	-	1323G1	0.47	11.94	0.39	9.91
2	33.6	High	-	1319-BK	1319	0.44	11.18	0.34	8.64
4	21.1	High	-	1319G4-BK	1319G4	0.44	11.18	0.29	7.37
6	13.3	High	-	1319G6-BK	1319G6	0.44	11.18	0.22	5.59



© 2018 Anderson Power Products, Inc. All rights reserved. APP®, Anderson Power Products®, A®, Powerpole®, SPEC Pak® and the APP Logo are registered trademarks of Anderson Power Products, Inc.



#### | PP120 SPECIFICATIONS |

Electrical		
Current Rating Amperes <sup>1</sup>	UL 1977	CSA
Singlepole UL 1977 (1/0 AWG)	240	155
2x2 Block UL 1977 (1/0 AWG)	200	110
Voltage Rating AC/DC		
UL 1977	600	
Dielectric Withstanding Voltage		
Volts AC	2,200	
Avg. Mated Contact Resistance Milliohms	1	
5 1/2" of #2 AWG wire	0.136	
UL Hot Plug Current Rating Amperes 4		
250 cycles at 120V DC	60A	

Materials	
Housing	
Plastic Resin	Polycarbonate
Contact Retention Spring	Stainless Steel
Housing Flammability Rating	
UL94	V-0
Glow Wire	960°C (GWFI) / 850°C (GWIT)
Contact	
Base	Copper Alloy
Plating	Silver
Contact Termination Methods	
Crimp <sup>3</sup>	Wire Contacts
Hand Solder	Wire Contacts

Mechanical		
Wire Size Range Wire Contacts with Bushings	<b>AWG</b> 10 to 1/0	mm <sup>2</sup> 5.3 to 53.5
Max. Wire Insulation Diameter	in. 0.600	<b>mm</b> 15.240
Operating Temperature <sup>2</sup>	<b>°F</b> -4° to 221°	°C -20° to 105°
Mating Cycles No Load by Plating Wire Contacts	<b>Silver (Ag)</b> 10,000	
Avg. Mating / Unmating Force	Lbf. 8	<b>N</b> 36
Min. Contact / Spring Retention Force	<b>Lbf</b> . 60	<b>N</b> 267

NOTE 1: See IEC 60664-1 for working voltage.

NOTE 2: Amp ratings are stated per position and based on all positions being fully loaded.

- ¹ Based on: 105°C rated or better cable of the largest size, Properly calibrated APP recommended tooling, and a 25°C ambient temperature. UL rating not to exceed the maximum operating temperature. CSA rating below a 30°C temperature rise.
- <sup>2</sup> Limited by the thermal properties of the connector plastic housing.
- <sup>3</sup> Use APP recommended tooling only. Alternate tools may adversely affect the performance of our connectors along with UL and CSA recognition.
- <sup>4</sup> Based on 2 housings blocked together.









### | IEC INFORMATION |

Connector Series	Configurations		Creepage / Clearance per IEC 60950-1	Material Group
	Single Pole	Unmated	4.36 mm	
PP120	Olligio i olo	Mated	4.36 mm	IIIa
	Stacked Powerpole®	Unmated	4.36 mm	
	Stacked Fowerpoles	Mated	4.36 mm	

Attributes	PP120
AMP Rating AC/DC  Voltage Rating AC/DC (Steady State)  Breaking Capacity -AMP Rating /Cycles  Voltage Rating (Breaking Capacity)  FINGER Safety - Mated only  Wire Size tested	120 400 V AC/DC ( Operational) 120 Amp / 10 Cycles 220 VDC IEC 60529 - IP20 50 mm <sup>2</sup>
Contact Series Tested Climatic Testing (Cold,Heat & MFG) Cycle Life Mechanical Strength Impact Temperature Range	1323G2 IEC 60512 Test -11j, 11i & 11g, IEC 60512 Test 9a - 5000 Cycles IEC 60512-5 @ 29.5 Inches - dropped 8 times -20 °C to 105 °C -4 °F to 221 °F


#### **Protection**


**Touch Safety with Wire Contacts** IEC 60529 IP10




NOTE 3: Refer to the Constructional Data form for additional information on our website., www.andersonpower.com


#### For Temperature Rise Above 60°C, Consult the Extended Temperature Rise Charts in the Appropriate Product Section on the Website.





#### Current - Temperature Derating per IEC 60512-5-2 Test 5B






#### POWERPOLE® PP120 ACCESSORIES |

#### **Mounting Clamp**

Mounting clamps can be used for fastening a block of Powerpole® 120 series housings to a panel. Connector blocks must be a complete square for the clamps to work properly. Fastening hardware not included.

Description	- Part Numbers -
Minimum Quantity	20 sets of 2
2 Pole	1464G1
3 Pole	1464G2








#### **Retaining Pins**

Retaining pins are used to keep stacked Powerpole® 120 series housings from separating. Retaining pins are inserted in the circular opening between two housings stacked side by side. Dimension B is +/- 0.015 in or 0.38 mm.

•	•					
				Dimensions		
			- A -		- B -	
Description	Part Nu	mbers	inches	mm	inches	mm
Minimum Quantity	1,000	100				
1 Block High	111812P7	110G19	0.196 / 0.207	4.98 / 5.26	0.560	14.220
2 Block High	111812P8	110G20	0.196 / 0.207	4.98 / 5.26	1.500	38.100



#### **Reducing Bushings**

Use with contact part number 1319-BK to allow a smaller wire to be used with the connector. Electrical capability is derated with smaller wire.

					Dimen	sions
					- II	D -
Contact Barrel Size	Wire Size	Pa	rt Numbers		inches	mm
Minimum Quantity		2,000	1,000	100 .		
#2 AWG [33.6 mm <sup>2</sup> ]	#4 AWG [21.2 mm²]	5919-BK	-	5919	0.28	7.11
#2 AWG [33.6 mm <sup>2</sup> ]	#6 AWG [16 mm²]	-	5920-BK	5920	0.23	5.84
#2 AWG [33.6 mm <sup>2</sup> ]	#10 - 8 AWG [5.3 - 8.4 mm <sup>2</sup> ]	5921-BK		5921	0.18	4.57



For environmentally sealed connector shells to hold Powerpole® 15-180 connectors, see SPEC Pak® product series on our website, www.andersonpower.com

www.andersonpower.com

.....









# Powerpole® - Tooling Information

Wire	Size	Reeled Pa	ed Part Numbers Reel		ntact Crimp Tool
AWG	mm²	Tin Plating	Silver Plating	APP Applicator	+ APP Press
	PP15 /	45 Flat W	iping Power	& Ground	
#16 / 20	1.3 / 0.52	262G1	262G2		
#16 / 20	1.3 / 0.52	269G2	N/A		
#12 / 16	3.3 / 1.3	261G1	N/A	TD0101	
#10 / 14	5.3 / 2.1	261G2	261G3	100101	115V= TE0101
#12 / 16	3.3 / 1.3	269G1	N/A		230V = TE0102
#10 / 14	5.3 / 2.1	269G3	N/A		2300 - 120102
#10 / 14	5.3 / 2.1	200G1L	200G3L		
#10 / 14	5.3 / 2.1	201G1H	N/A	TD0102	
#10 / 14	5.3 / 2.1	1830G1	1830G2		

<sup>\*</sup> APP applicators are mechanical feed style and do not require an air feed kit.

Wire Size Loose Piece Part Numbers Loose					se Piece	Contac	ct Crimp	Tool
AWG	mm²	Tin Plating	Silver Plating	Hand Tool o	Pneumatic Bench r Tool		Locator	Number of Crimps
		PP1	5 / 45 Flat Wip	ing Pow	er & Groun	d		
#16 / 20	1.3 / 0.52	N/A	1332					
#12 / 16	3.3 / 1.3	N/A	1331	1309G2 or				
#16 / 20	1.3 / 0.52	262G1-LPBK	262G2-LPBK	1309G8				
#16 / 20	1.3 / 0.52	269G2-LPBK	N/A					
#12 / 16	3.3 / 1.3	261G1-LPBK	N/A					
#10 / 14	5.3 / 2.1	261G2-LPBK	261G3-LPBK	1309G3 or	N/A	N/A	N/A	Single
#12 / 16	3.3 / 1.3	269G1-LPBK	N/A	1309G8				
#10 / 14	5.3 / 2.1	269G3-LPBK	N/A					
#10 / 14	5.3 / 2.1	200G1L-LPBK	200G3L-LPBK	1309G6				
#10 / 14	5.3 / 2.1	201G1H-LPBK	N/A	or				
310 / 14	5.3 / 2.1	1830G1-LPBK	1830G2-LPBK	1309G8				
			PF	75				
#6	13.3		1307				1389G6	
,,,	10.0		5900	-			100000	
#8	8.4		1875G1			1388G6	1389G21	
		5952	1387G1		1389G6	Single		
#10 / 12	E 2 / 2 2	IN/A	1875G2	150504	1307 61	130701	1389G21	Sirigie
#10 / 12	5.5 / 5.5		5953			40000=	1389G6	
			5915 1875G3			1388G7	1389G21	
			1875G3	120			1309021	
1/0	53.5		1323G2	120				
#1	42.4		1323G1			1388G3		
#2	33.6	N/A	1319	1368	1387G1		1389G4	Single
#4	21.2	14// 1		Series	1007 01	1388G4	.5000 +	Cirigic
	13.3		1319G4			100004		
#6	13.3		1319G6	180				
3/0	85		1328G2	.00				
2/0	53.5					1303G12		
1/0	53.5		1328G1 1382					
#1	42.4	N/A	1347	1368	1387G2	1303G13	1304G32	Double
#2	33.6		1383	Series		2 1303013		
#4	21.1		1384					
#6	13.3		1348		1387G1	1388G4	1389G3	Single

<sup>1.</sup> NOTE: See website for the most current information.

<sup>2.</sup> NOTE: Insertion / Extraction fool for PP15/45 contacts = 111038G2