

MICROMASTER 4 BRAKING RESISTOR 380-480 V 56R 13000 W  
PK 650 W CONT 285 X 185 X 150 MM H X W X D IP20



Figure similar

Order number	6SE6400-4BD16-5CA0
Phase number / of the input voltage	3
Type of voltage / of the input voltage	AC
Input voltage	380 ... 480
Active power consumption / Rated value	0.65 kW
• maximum	11 kW
Type of electrical connection / for power cable	shielded lead
Connectable conductor cross-section / for power cable	1.5 mm <sup>2</sup>
Design of the temperature switch	Normally closed contact
Input voltage / of the temperature switch / with AC / maximum	250 V
Input current / of the temperature switch / with AC / maximum	2.5 A
Connectable conductor cross-section / on the temperature switch / maximum	2.5 mm <sup>2</sup>
Protection class IP	IP20
Electrical resistance / of the braking resistor	56 Ω
Width	185 mm
Height	285 mm
Depth	150 mm
Net weight	3.8 kg

### Further information

#### Information und Download Center

[https://www.automation.siemens.com/mcms/infocenter/content/en/Pages/order\\_form.aspx](https://www.automation.siemens.com/mcms/infocenter/content/en/Pages/order_form.aspx)

#### Technical documentation

<http://w3.siemens.com/mcms/mc-solutions/en/motion-control/support/technical-documentation/Pages/technical-documentation.aspx>

**Industry Mall**

<https://eb.automation.siemens.com/mall/en/WW/Catag/Product/6SE64004BD165CA0/all>

**Industry Online Support**

<http://support.automation.siemens.com/WW/view/en/6SE64004BD165CA0/all>