
GeneSic SEMICONDUCTOR

Silicon Carbide Schottky Diode

 $V_{RRM} = 650 V$ $I_{F (Tc = 163^{\circ}C)} = 6 A$ $Q_{C} = 15 nC$

Features

- Gen5 Thin Chip Technology for Low V_F
- Low Conduction Losses for All Load Conditions
- Superior Figure of Merit Q_C/I_F
- Enhanced Surge Current Robustness
- Low Thermal Resistance
- Temperature Independent Fast Switching
- Positive Temperature Coefficient of V_F
- High dV/dt Ruggedness



Advantages

- Optimal Price Performance
- Improved System Efficiency
- Enables Extremely Fast Switching
- Reduced Cooling Requirements
- Increased System Power Density
- Zero Reverse Recovery Current
- Easy to Parallel without Thermal Runaway
- High System Reliability

Applications

- Switched Mode Power Supply (SMPS)
- Solar Inverter
- Server and Telecom Power Supply
- Battery Charger
- Uninterruptible Power Supply (UPS)


Absolute Maximum Ratings (At T _C = 25°C Unless Otherwise Stated)							
Parameter	Symbol	Conditions	Values	Unit	Note		
Repetitive Peak Reverse Voltage	V_{RRM}		650	V			
		$T_C = 100^{\circ}C, D = 1$	17				
Continuous Forward Current	l _F	$T_C = 135^{\circ}C, D = 1$	12	Α	Fig. 4		
		$T_C = 163^{\circ}C, D = 1$	6				
Non-Repetitive Peak Forward Surge Current, Half Sine	1	$T_C = 25^{\circ}C$, $t_P = 10 \text{ ms}$	33	Α			
Wave	I _{F,SM}	$T_C = 150$ °C, $t_P = 10$ ms	27				
Repetitive Peak Forward Surge Current, Half Sine Wave	I	T_C = 25°C, t_P = 10 ms	20				
Repetitive Peak Forward Surge Current, Half Sine Wave	I _{F,RM}	$T_C = 150^{\circ}C$, $t_P = 10 \text{ ms}$	14	Α			
Non-Repetitive Peak Forward Surge Current	I _{F,MAX}	T_C = 25°C, t_P = 10 μ s	165	Α			
i ² t Value	∫i²dt	$T_C = 25^{\circ}C$, $t_P = 10 \text{ ms}$	5.445	A ² s			
Non-Repetitive Avalanche Energy	E _{AS}	L = 4.4 mH, I _{AS} = 6 A	79	mJ			
Diode Ruggedness	dV/dt	V _R = 0 ~ 520 V	200	V/ns			
Power Dissipation	Ртот	T _C = 25°C	133	W	Fig. 3		
Operating and Storage Temperature	T_j , T_{stg}		-55 to 175	°C			




Electrical Characteristics								
Parameter	Symbol	Conditions		Values		Unit	Note	
raiailletei	Зуший			Min.	Тур.	Max.	Oilit	Note
Diode Forward Voltage V _F		I _F = 6 A, T _j = 25°C			1.25	1.35	٧	Fig. 1
Diode Forward Voltage V _F	۷F	I _F = 6 A, T _j = 150°C			1.64		V	Fig. 1
Reverse Current IR	l _a	V _R = 650 V, 1	_j = 25°C		1	5		Fig. 2
Reverse Guitein	erse Current I _R	$V_R = 650 \text{ V, } T_j = 150 ^{\circ}\text{C}$			42		μΑ	riy. Z
Total Conscitive Charms	0.		V _R = 200 V		10		nC	Fig. 7
Total Capacitive Charge	Qc	$I_{F} \leq I_{F,MAX}$	$V_{R} = 400 V$		15		IIC	rig. /
Switching Time	+-	dI _F /dt = 200 A/μs	$V_R = 200 V$		< 10		no	
	ts		$V_{R} = 400 V$		< 10		ns	
Total Capacitance C	V _R = 1 V, f = 1MHz			279		nE	Fig. 6	
	C	$V_R = 400 \text{ V, f} = 1 \text{MHz}$			20		þг	Fig. 0
Total Capacitance	C						pF	Fig. 6

Thermal/Package Characteristics							
Symbol	Conditions	Values			Unit	Note	
	Conditions	Min.	Тур.	Max.	- Unit	Note	
R_{thJC}			1.13		°C/W	Fig. 9	
W _T			0.3		g		
	Symbol R _{thJC}	Symbol Conditions	Symbol Conditions Min.	$\begin{tabular}{c} Symbol & Conditions & \hline \hline & Values \\ \hline Min. & Typ. \\ \hline R_{thJC} & 1.13 \\ \hline \end{tabular}$	Symbol Conditions Values Min. Typ. Max. Typ. Max. Typ. T	$\begin{tabular}{c cccc} Symbol & Conditions & \hline & Values & & Unit \\ \hline Min. & Typ. & Max. & \\ \hline R_{thJC} & 1.13 & °C/W \\ \hline \end{tabular}$	









 $I_F = f(V_F, T_j); t_P = 250 \mu s$

Figure 2: Typical Reverse Characteristics



 $I_R = f(V_R, T_j)$

Figure 3: Power Derating Curves



 $I_F = f(T_C); D = t_P/T; T_j \le 175^{\circ}C; f_{SW} > 10kHz$










Figure 5: Current Derating Curves (Maximum V_F)



 $I_F = f(T_C); D = t_P/T; T_j \le 175^{\circ}C; f_{SW} > 10kHz$

Figure 6: Typical Junction Capacitance vs Reverse Voltage Characteristics



 $C = f(V_R)$; f = 1MHz

Figure 7: Typical Capacitive Charge vs Reverse Voltage Characteristics






Figure 8: Typical Capacitive Energy vs Reverse Voltage Characteristics



 $E_C = f(V_R)$; f = 1MHz




Figure 9: Transient Thermal Impedance



 $Z_{th,jc} = f(t_P,D); D = t_P/T$

Figure 10: Forward Curve Model



Forward Voltage, $V_F(V)$

 $I_F = f(V_F, T_j)$

Forward Curve Model Equation:

 $I_F = (V_F - V_{BI})/R_{DIFF}(A)$

Built-In Voltage (V_{BI}):

$$V_{BI}(T_j) = m \times T_j + n (V)$$

 $m = -0.00124 (V/^{\circ}C)$
 $n = 0.72 (V)$

Differential Resistance (RDIFF):


$$R_{DIFF}(T_j) = a \times T_j^2 + b \times T_j + c (\Omega)$$

 $a = 1.6e-06 (\Omega/^{\circ}C^2)$
 $b = 0.000454 (\Omega/^{\circ}C)$
 $c = 0.0802 (\Omega)$

Forward Power Loss Equation:

 $P_{LOSS} = V_{BI}(T_i) \times I_{AVG} + R_{DIFF}(T_i) \times I_{RMS}^2$





NOTE

- 1. CONTROLLED DIMENSION IS INCH. DIMENSION IN BRACKET IS MILLIMETER.
- 2. DIMENSIONS DO NOT INCLUDE END FLASH, MOLD FLASH, MATERIAL PROTRUSIONS.





Compliance

RoHS Compliance

The levels of RoHS restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU Directive 2011/65/EC (RoHS 2), as adopted by EU member states on January 2, 2013 and amended on March 31, 2015 by EU Directive 2015/863. RoHS Declarations for this product can be obtained from your GeneSiC representative.

REACH Compliance

REACH substances of high concern (SVHCs) information is available for this product. Since the European Chemical Agency (ECHA) has published notice of their intent to frequently revise the SVHC listing for the foreseeable future, please contact a GeneSiC representative to insure you get the most up-to-date REACH SVHC Declaration. REACH banned substance information (REACH Article 67) is also available upon request.

Disclaimer

GeneSiC Semiconductor, Inc. reserves right to make changes to the product specifications and data in this document without notice. GeneSiC disclaims all and any warranty and liability arising out of use or application of any product. No license, express or implied to any intellectual property rights is granted by this document.

Unless otherwise expressly indicated, GeneSiC products are not designed, tested or authorized for use in life-saving, medical, aircraft navigation, communication, air traffic control and weapons systems, nor in applications where their failure may result in death, personal injury and/or property damage.

Related Links

SPICE Models: https://www.genesicsemi.com/sic-schottky-mps/GE06MPS06E/GE06MPS06E_SPICE.zip
 PLECS Models: https://www.genesicsemi.com/sic-schottky-mps/GE06MPS06E/GE06MPS06E_PLECS.zip
 CAD Models: https://www.genesicsemi.com/sic-schottky-mps/GE06MPS06E/GE06MPS06E_3D.zip

• Evaluation Boards: https://www.genesicsemi.com/technical-support

Reliability: https://www.genesicsemi.com/reliability
 Compliance: https://www.genesicsemi.com/compliance
 Quality Manual: https://www.genesicsemi.com/quality

Revision History

Date	Revision	Comments	Supersedes
Jul. 27, 2020	Rev 1	Initial Release	



www.genesicsemi.com/sic-schottky-mps/

