Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION



1855A Coax - Sub-Miniature

For more Information please call

1-800-Belden1



General Description:

23 AWG solid .023" bare copper conductor, gas-injected foam HDPE insulation, Duofoil® + tinned copper braid shield (95% coverage), PVC jacket.

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Duofoil®	Таре	Aluminum Foil-Polyester Tape-Aluminum Foil	100
2		Braid	TC - Tinned Copper	95

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cable

Overall Nominal Diameter: 0.159 in.

Med	Mechanical Characteristics (Overall)				
	Operating Temperature Range:	-30°C To +75°C			
	UL Temperature Rating:	75°C			
	Bulk Cable Weight:	17 lbs/1000 ft.			
	Max. Recommended Pulling Tension:	40 lbs.			
	Min. Bend Radius/Minor Axis:	1.500 in.			

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards	&	Environmental	Programs
----------------------	---	---------------	-----------------

NEC/(UL) Specification:	CMR
CEC/C(UL) Specification:	CMG
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
	.,

Page 1 of 3 01-05-2017

Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION



1855A Coax - Sub-Miniature

MII Order #39 (China RoHS):	Yes		
RG Type:	Sub-miniature 59/U		
Flame Test			
UL Flame Test:	UL1666 Vertical Shaft		
CSA Flame Test:	FT4		
Suitability	Suitability		
Suitability - Indoor:	Yes		
Plenum/Non-Plenum			
Plenum (Y/N):	No		
Plenum Number:	1855P		

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:



Nom. Inductance:



Nom. Capacitance Conductor to Shield:



Nominal Velocity of Propagation:



Nominal Delay:



Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft) 20.1

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
1.000	0.390
3.580	0.780
5.000	0.920
6.000	1.000
7.000	1.080
10.000	1.200
12.000	1.300
25.000	1.800
67.500	2.830
71.500	2.930
88.500	3.220
100.000	3.390
135.000	3.840
143.000	4.000
180.000	4.410
270.000	5.440
360.000	6.340
540.000	7.850
720.000	9.150
750.000	9.310
1000.000	10.890
1500.000	13.380
2000.000	15.640
2250.000	16.680
3000.000	19.650
4500.000	24.350
6000.000	28.970

Max. Operating Voltage - UL:

Voltage 300 V RMS

Page 2 of 3 01-05-2017

Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION



1855A Coax - Sub-Miniature

Other Electrical Characteristic 1:

IDR Impedance: 75 +/- 1.5 Ohms

Other Electrical Characteristic 2:

Return Loss: Fixed bridge and termination.

Minimum Return Loss

Start Freq. (MHz)	Stop Freq. (MHz)	Min. RL (dB)
5.000	1600.000	23.000
1601.000	4500.000	21.000
4500.000	6000.000	15.000

Sweep Test

Sweep Testing:

100% Sweep tested 5 MHz to 6 GHz.

Misc. Information (Overall)

Notes (Overall)

Notes: Also available in 4.5 GHz multi-coax bundled versions. See 7787A through 7792A.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1855A N3UN1000	1,000 FT	21.000 LB	GREEN, MIL		#23 PE/GIFHDPE SH FR PVC
1855A N3U1000	1,000 FT	19.000 LB	GREEN, MIL	С	#23 PE/GIFHDPE SH FR PVC
1855A 001N1000	1,000 FT	21.000 LB	BROWN		#23 PE/GIFHDPE SH FR PVC
1855A 0011000	1,000 FT	19.000 LB	BROWN	С	#23 PE/GIFHDPE SH FR PVC
1855A 002N1000	1,000 FT	21.000 LB	RED		#23 PE/GIFHDPE SH FR PVC
1855A 0021000	1,000 FT	19.000 LB	RED	С	#23 PE/GIFHDPE SH FR PVC
1855A 003N1000	1,000 FT	21.000 LB	ORANGE		#23 PE/GIFHDPE SH FR PVC
1855A 0031000	1,000 FT	19.000 LB	ORANGE	С	#23 PE/GIFHDPE SH FR PVC
1855A 004N1000	1,000 FT	21.000 LB	YELLOW		#23 PE/GIFHDPE SH FR PVC
1855A 0041000	1,000 FT	19.000 LB	YELLOW	С	#23 PE/GIFHDPE SH FR PVC
1855A 006N1000	1,000 FT	21.000 LB	BLUE, LIGHT		#23 PE/GIFHDPE SH FR PVC
1855A 0061000	1,000 FT	19.000 LB	BLUE, LIGHT	С	#23 PE/GIFHDPE SH FR PVC
1855A 007N1000	1,000 FT	21.000 LB	VIOLET		#23 PE/GIFHDPE SH FR PVC
1855A 0071000	1,000 FT	19.000 LB	VIOLET	С	#23 PE/GIFHDPE SH FR PVC
1855A 008N1000	1,000 FT	21.000 LB	GRAY		#23 PE/GIFHDPE SH FR PVC
1855A 0081000	1,000 FT	19.000 LB	GRAY	С	#23 PE/GIFHDPE SH FR PVC
1855A 009N1000	1,000 FT	21.000 LB	WHITE		#23 PE/GIFHDPE SH FR PVC
1855A 0091000	1,000 FT	19.000 LB	WHITE	С	#23 PE/GIFHDPE SH FR PVC
1855A 010N1000	1,000 FT	21.000 LB	BLACK		#23 PE/GIFHDPE SH FR PVC
1855A 0101000	1,000 FT	19.000 LB	BLACK	С	#23 PE/GIFHDPE SH FR PVC
1855A 010500	500 FT	9.500 LB	BLACK		#23 PE/GIFHDPE SH FR PVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 13 Revision Date: 06-17-2016

© 2017 Belden, Inc All Rights Reserved

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its bublication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).

Page 3 of 3