

# **DATA SHEET**

THICK FILM CHIP RESISTORS **Precision grade** 

**RE** series

0.1%, 0.5%, 1%, TC 50 sizes 0201/0402/0603/0805/1206 RoHS compliant & Halogen Free







RE

#### SCOPE

**YAGEO** 

This specification describes RE0201 to RE1206 ultra precision chip resistors with lead-free terminations made by thick film process.

#### **APPLICATIONS**

- Converters
- Printer equipment
- Server board
- Telecom
- Consumer

#### **FEATURES**

- Halogen Free Epoxy
- RoHS compliant
- Reducing environmentally hazardous wastes
- High component and equipment reliability
- · Non-forbidden material used in products/production
- Moisture sensitivity level: MSL I

#### ORDERING INFORMATION - GLOBAL PART NUMBER & 12NC

Both part numbers are identified by the series, size, tolerance, packing type, temperature coefficient, taping reel and resistance value.

#### YAGEO BRAND ordering code

#### GLOBAL PART NUMBER (PREFERRED)

# RE XXXX X X X XX XXXX L

(2) (3) (4) (5) (1)

#### (I) SIZE

0201 / 0402 / 0603 / 0805 / 1206

#### (2) TOLERANCE

 $B = \pm 0.1\%$ 

 $D = \pm 0.5\%$ 

 $F = \pm 1\%$ 

#### (3) PACKAGING TYPE

R = Paper/PE taping reel

# (4) TEMPERATURE COEFFICIENT OF RESISTANCE

 $E = \pm 50 \text{ ppm/}^{\circ}\text{C}$ 

#### (5) TAPING REEL

07 = 7 inch dia. Reel

10 = 10 inch dia, Reel

13 = 13 inch dia, Reel

#### (6) RESISTANCE VALUE

There are 2~4 digits indicated the resistor value. Letter R/K/M is decimal point, no need to mention the last zero after R/K/M, e.g. I K2, not I K20.

Detailed resistance rules show in table of "Resistance rule of global part number".

#### (7) DEFAULT CODE

Letter L is system default code for order only (Note)

#### Resistance rule of global part number

Resistance code rule	Example
XXRX	IOR = IO Ω
(10 to 97.6 $\Omega$ )	97R6 = 97.6 $Ω$
XXXR (100 to 976 Ω)	100R = 100 Ω
XKXX	IK = 1,000 Ω
(1 to 9.76 K <b>Ω)</b>	9K76 = 9760 $Ω$
XMXX (Ι ΜΩ)	IM = 1,000,000 Ω

# **ORDERING EXAMPLE**

The ordering code of a RE0603 chip resistor, TC 50 value 56  $\Omega$  with ±0.5% tolerance, supplied in 7-inch tape reel is: RE0603DRE0756RL.

#### NOTE

- I. All our R-Chip products meet RoHS compliant and Halogen Free. "LFP" of the internal 2D reel label mentions "Lead Free Process"
- 2. On customized label, "LFP" or specific symbol can be printed






**Chip Resistor Surface Mount** RE SERIES 0201 to 1206

### <u>MARKING</u>

# RE0805 / RE1206




Either resistance in E-24 or E-96: 4 digits

First three digits for significant figure and 4th digit for number of zeros

#### **RE0603**



1%, 0.5%, 0.1% E24 exception values 10/11/13/15/20/75 of E24 series



1%, 0.5%, 0.1% E96 refer to EIA-96 marking method, including values 10/11/13/15/20/75 of E24 series

#### RE0201/0402



No marking

For further marking information, please see special data sheet "Chip resistors marking".

#### CONSTRUCTION


The resistors are constructed out of a high-grade ceramic body. Internal metal electrodes are added at each end and connected by a resistive layer. The resistive layer is adjusted to give the approximate required resistance and laser cutting of this resistive layer that achieves tolerance trims the value. The resistive layer is covered with a protective coat and printed with the resistance value. Finally, the two external terminations (matte tin) are added. See fig. 5.

# **DIMENSION**

**Table I** For outlines see fig. 5

TYPE	L (mm)	W (mm)	H (mm)	I <sub>I</sub> (mm)	l <sub>2</sub> (mm)
RE0201	0.60 ±0.03	0.30 ±0.03	0.23 ±0.03	0.10 ±0.05	0.15 ±0.05
RE0402	1.00 ±0.05	0.50 ±0.05	0.32 ±0.05	0.20 ±0.10	0.25 ±0.10
RE0603	1.60 ±0.10	0.80 ±0.10	0.45 ±0.10	0.25 ±0.15	0.25 ±0.15
RE0805	2.00 ±0.10	1.25 ±0.10	0.50 ±0.10	0.35 ±0.20	0.35 ±0.20
RE1206	3.10 ±0.10	1.60 ±0.10	0.55 ±0.10	0.45 ±0.20	0.45 ±0.20

#### **OUTLINES**





RE SERIES 0201 to 1206

#### **ELECTRICAL CHARACTERISTICS**

#### Table 2

TYPE	RESISTANCE RANGE (E24/E96)	OPERATING TEMPERATURE RANGE	POWER RATING	MAXIMUM WORKING VOLTAGE	DIELECTRIC WITHSTAND VOLTAGE	MAXIMUM OVERLOAD VOLTAGE	TEMPERATURE COEFFICIENT OF RESISTANCE
RE0201	100 $\Omega$ to 1 M $\Omega$	-55 °C to +155 °C	1/20W	25 V	50 V	50 V	±50 ppm/°C
RE0402	10 $\Omega$ to 1 $M\Omega$	-55 °C to +155 °C	1/16 W	50 V	100 V	100 V	±50 ppm/°C
RE0603	10 $\Omega$ to 1 $M\Omega$	-55 °C to +155 °C	1/10 W	75 V	150 V	150 V	±50 ppm/°C
RE0805	10 $\Omega$ to 1 $M\Omega$	-55 °C to +155 °C	1/8 W	150 V	300 V	300 V	±50 ppm/°C
RE1206	10 $\Omega$ to 1 $M\Omega$	-55 °C to +155 °C	1/4 W	200 V	500 V	400 V	±50 ppm/°C

#### NOTE

The maximum working voltage that may be continuously applied to the resistor element, see "IEC publication 60115-8"

#### FOOTPRINT AND SOLDERING PROFILES

For recommended footprint and soldering profiles, please see the special data sheet "Chip resistors mounting".

#### PACKING STYLE AND PACKAGING QUANTITY

Table 3 Packing style and packaging quantity

PACKING STYLE	REEL DIMENSION	RE0201	RE0402	RE0603	RE0805	RE1206
Paper/PE taping reel (R)	7" (178 mm)	10,000	10,000	5,000	5,000	5,000
	10" (254 mm)	20,000	20,000	10,000	10,000	10,000
	13" (330 mm)	50,000	50,000	20,000	20,000	20,000

# NOTE

1. For Paper/PE tape and reel specification/dimensions, please see the special data sheet "Chip resistors packing"

#### **FUNCTIONAL DESCRIPTION**

# **POWER RATING**

Each type rated power at 70°C: RE0201=1/20W, RE0402=1/16W, RE0603=1/10W, RE0805=1/8 W, RE1206=1/4W

#### **RATED VOLTAGE**

The DC or AC (rms) continuous working voltage corresponding to the rated power is determined by the following formula:

$$V = \sqrt{(PxR)}$$


or max. working voltage whichever is less

Where

V=Continuous rated DC or AC (rms) working voltage (V)

P=Rated power (W)

R=Resistance value ( $\Omega$ )





# Chip Resistor Surface Mount RE SERIES 0201 to 1206

# TESTS AND REQUIREMENTS

**Table 4** Test condition, procedure and requirements

TEST	TEST METHOD	PROCEDURE	REQUIREMENTS
Life/Endurance	IEC 60115-1 7.1	At 70±2 °C for 1,000 hours, RCWV applied	±(3%+0.05 Ω)
	MIL-STD-202 Method 108	for 1.5 hours on, 0.5 hour off, still air required	
High Temperature Exposure	MIL-STD-202 Method 108	I,000 hours at 155±5 °C, unpowered	±(3%+0.05 Ω)
Moisture Resistance	MIL-STD-202 Method 106	Each temperature / humidity cycle is defined at 8 hours, 3 cycles / 24 hours for I 0d. with 25 °C / 65 °C 95% R.H, without steps 7a & 7b, unpowered	±(3%+0.05 Ω)
		Parts mounted on test-boards, without condensation on parts	
		Measurement at 24±2 hours after test conclusion	
Thermal Shock	MIL-STD-202 Method 107	-55/+125 °C Number of cycles required is 300.	±(1%+0.05 Ω)
		Devices mounted	
		Maximum transfer time is 20 seconds. Dwell time is 15 minutes. Air – Air	
Short Time	IEC60115-1 8.1	2.5 times of rated voltage or maximum	±(1%+0.05 Ω)
Overload		overload voltage whichever is less for 5 sec at room temperature	No visible damage
Board Flex/ Bending	IEC 60115-1 9.8	Chips mounted on a 100mm×40mm glass	±(1%+0.05 Ω)
		epoxy resin PCB (FR4)	No visible damage
		Bending: see table 5 for each size  Bending time: 60±5 seconds	





# Chip Resistor Surface Mount RE SERIES 0201 to 1206

TEST	TEST METHOD	PROCEDURE	REQUIREMENTS
Humidity	IEC 60115-1 10.4	Steady state for 1000 hours at 40 °C / 95% R.H. RCWV applied for 1.5 hours of and 0.5 hour off	$\pm (3\% + 0.05~\Omega)$
Solderability		Floridad Todays and had	\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\
- Wetting	J-STD-002 test B1	Electrical Test not required  Magnification 50X	Well tinned (≥95% covered) No visible damage
		SMD conditions:	
		I <sup>st</sup> step: method BI, aging 4 hours at I55°C dry heat	
		2 <sup>nd</sup> step: leadfree solder bath at 245±3° Dipping time: 3±0.5 seconds	С
- Leaching	J-STD-002 test D	Leadfree solder, 260 °C, 30 seconds immersion time	No visible damage
- Resistance to Soldering Heat	MIL-STD-202 Method 210	Condition B, no pre-heat of samples. Leadfree solder, 260 °C, 10 seconds	$\pm$ (1%+0.05 $\Omega$ ) No visible damage
		immersion time Procedure 2 for SMD: devices fluxed ancleaned with isopropanol	d
Table 5 Bending for	r sizes 0201 to 1206		
TYPE	RE0201	RE0402 RE0603	RE0805 RE1206

5

3

3



Specification (mm)

5

2



# Chip Resistor Surface Mount RE SERIES 0201 to 1206

# REVISION HISTORY

REVISION	DATE	CHANGE NOTIFICATION	DESCRIPTION
Version 7	Aug. 03, 2022	-	- 12 dimension updated, for size I 206.
Version 6	May 31, 2017	-	- Add 10" packing
Version 5	Feb. 24, 2017	-	- Delete 125°C in derating curve
Version 4	May 03, 2016	-	- Update 0201 resistor value
Version 3	Jan. 26, 2015	-	- Update Working Voltage
Version 2	May 11, 2015	-	- Update test and requirements
Version I	Jan 23, 2014	-	<ul><li>Add RE0201</li><li>Add 0.1%</li><li>Update TEST AND REQUIREMENTS, add Humidity test</li></ul>
Version 0	Dec 10, 2010	-	- New datasheet for thick film ultra precision chip resistors sizes of 0402/0603/0805/1206, 0.5%, 1%, TC50 with lead-free terminations



Chin Resistor Surface Mount | RE | SERIES | 0201 to 1206

#### LEGAL DISCLAIMER

YAGEO, its distributors and agents (collectively, "YAGEO"), hereby disclaims any and all liabilities for any errors, inaccuracies or incompleteness contained in any product related information, including but not limited to product specifications, datasheets, pictures and/or graphics. YAGEO may make changes, modifications and/or improvements to product related information at any time and without notice.

YAGEO makes no representation, warranty, and/or guarantee about the fitness of its products for any particular purpose or the continuing production of any of its products. To the maximum extent permitted by law, YAGEO disclaims (i) any and all liability arising out of the application or use of any YAGEO product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for a particular purpose, non -infringement and merchantability.

YAGEO products are designed for general purpose applications under normal operation and usage conditions. Please contact YAGEO for the applications listed below which require especially high reliability for the prevention of defects which might directly cause damage to the third party's life, body or property: Aerospace equipment (artificial satellite, rocket, etc.), Atomic energy-related equipment, Aviation equipment, Disaster prevention equipment, crime prevention equipment, Electric heating apparatus, burning equipment, Highly public information network equipment, data-processing equipment, Medical devices, Military equipment, Power generation control equipment, Safety equipment, Traffic signal equipment, Transportation equipment and Undersea equipment, or for any other application or use in which the failure of YAGEO products could result in personal injury or death, or serious property damage. Particularly YAGEO Corporation and its affiliates do not recommend the use of commercial or automotive grade products for high reliability applications or manned space flight.

Information provided here is intended to indicate product specifications only. YAGEO reserves all the rights for revising this content without further notification, as long as products are unchanged. Any product change will be announced by PCN.

