

BLINDNIETE


SENKKOPF MIT GERILLTEM NIETDORN (~ DIN EN ISO 15984)

BLIND RIVETS

COUNTERSUNK HEAD WITH GROOVED MANDREL (~ DIN EN ISO 15984)


RIVETS AVEUGLES

AVEUGLES TÊTE FRAISÉE AVEC CLOU CANNELÉ (~ DIN EN ISO 15984)











Edelstahl A2 [1.4301]
Stainless steel A2 [AISI 304]
Acier inox A2 [1.4301]

Edelstahl A2 [1.4301]
Stainless steel A2 [AISI 304]
Acier inox A2 [1.4301]











Ø 3,0 mm

D1 = 3,0 + 0,08 / - 0,1 mm
D2 = 6,0 + 0 / - 0,4 mm
k = -
d = 1,9 mm
P ≥ 27,0 mm
L = + 1,0 / - 0,2 mm
 3,1 mm


	F-Max						
3,0 x 6,0 mm	10,4 mm	1,0 - 3,0 mm	70351 30600	1600 N	2000 N	1000	10000
3,0 x 8,0 mm	12,4 mm	3,0 - 5,0 mm	70351 30800			1000	10000
3,0 x 10,0 mm	14,4 mm	5,0 - 7,0 mm	70351 30100			1000	10000
3,0 x 12,0 mm	16,4 mm	7,0 - 9,0 mm	70351 30120			1000	10000








Ø 3,2 mm

D1 = 3,2 + 0,08 / - 0,1 mm
D2 = 6,0 + 0 / - 0,4 mm
k = -
d = 1,9 mm
P ≥ 27,0 mm
L = + 1,0 / - 0,2 mm
 3,3 mm


	F-Max						
3,2 x 6,0 mm	10,9 mm	1,0 - 3,0 mm	70351 32600	1800 N	2500 N	1000	10000
3,2 x 8,0 mm	12,9 mm	3,0 - 5,0 mm	70351 32800			1000	10000
3,2 x 10,0 mm	14,9 mm	5,0 - 7,0 mm	70351 32100			1000	10000
3,2 x 12,0 mm	16,9 mm	7,0 - 9,0 mm	70351 32120			1000	10000
3,2 x 14,0 mm	18,9 mm	8,0 - 11,0 mm	70351 32140			1000	10000








Ø 4,0 mm

D1 = 4,0 + 0,08 / - 0,15 mm
D2 = 7,5 + 0 / - 0,5 mm
k = -
d = 2,5 mm
P ≥ 27,0 mm
L = + 1,0 / - 0,2 mm
 4,1 mm

	F-Max						
4,0 x 6,0 mm	10,9 mm	1,0 - 2,5 mm	70351 40600	3100 N	3800 N	1000	10000
4,0 x 8,0 mm	12,9 mm	2,5 - 4,5 mm	70351 40800			1000	10000
4,0 x 10,0 mm	14,9 mm	4,5 - 6,5 mm	70351 40100			1000	10000
4,0 x 12,0 mm	16,9 mm	6,5 - 8,5 mm	70351 40120			500	5000
4,0 x 14,0 mm	18,9 mm	8,5 - 10,5 mm	70351 40140			500	5000
4,0 x 16,0 mm	20,9 mm	9,5 - 12,0 mm	70351 40160			500	5000
4,0 x 18,0 mm	22,9 mm	12,0 - 14,0 mm	70351 40180			500	5000
4,0 x 20,0 mm	24,9 mm	14,0 - 16,0 mm	70351 40200			500	5000

Ø 4,8 mm

D1 = 4,8 + 0,08 / - 0,15 mm
D2 = 9,0 + 0 / - 0,5 mm
k = -
d = 3,0 mm
P ≥ 27,0 mm
L = + 1,0 / - 0,2 mm
 4,9 mm

	F-Max						
4,8 x 8,0 mm	13,4 mm	1,5 - 4,0 mm	70351 48800	4500 N	6000 N	500	5000
4,8 x 10,0 mm	15,4 mm	4,0 - 6,0 mm	70351 48101			500	5000
4,8 x 12,0 mm	17,4 mm	6,0 - 8,0 mm	70351 48120			500	5000
4,8 x 14,0 mm	19,4 mm	8,0 - 9,5 mm	70351 48140			500	5000
4,8 x 16,0 mm	21,4 mm	9,5 - 11,0 mm	70351 48160			500	5000
4,8 x 18,0 mm	23,4 mm	11,0 - 13,0 mm	70351 48180			500	5000
4,8 x 20,0 mm	25,4 mm	12,0 - 15,0 mm	70351 48200			500	5000
4,8 x 21,0 mm	26,4 mm	13,0 - 16,0 mm	70351 48210			500	5000
4,8 x 25,0 mm	30,4 mm	15,0 - 20,0 mm	70351 48250			250	2500