

SVJC boring bar, offset, HSS positive, left-hand

For face and longitudinal turning with CC indexable insert

ATORN[®]

Application


For face and longitudinal turning with CC indexable insert 80°.

Version

- precision-manufactured **HSS** boring bar, with inner cooling, offset, C type, 95° pitch angle, 80° tip angle, 7° clearance angle

Advantage

- Universal use for face and longitudinal turning
- Positive body geometry ensures low cutting forces
- Very high rigidity and very good cut quality due to HSS base material



Art. No.	17846 196
ISO name	AH 1012 J SCLC R/L 06
Min. bore diameter	14 mm
Tapered diameter	10 mm
Shaft diameter	12 mm
Clearance length	38 mm
Length	110 mm
Clamping surface height	11 mm
Programming size	7 mm
Suitable for indexable inserts	CC.. 06..
Tool design	Left
DIN	8024

EAN-Code

4050293111064