according to Regulation (EC) No. 1907/2006

Everbuild Glass Cleaner





Revision Date 30.01.2018

Version 1.0

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Trade name : Everbuild Glass Cleaner

1.2 Relevant identified uses of the substance or mixture and uses advised against

1.3 Details of the supplier of the safety data sheet

Company : Everbuild – A Sika Company

Site 41

Knowsthorpe Way

Cross Green Industrial Estate

Leeds

West Yorkshire LS9 0SW

United Kingdom

Telephone : 0113 240 3456

E-mail address : everbuild.sds@uk.sika.com

1.4 Emergency telephone number

Emergency telephone num-

ber

: 0044 113 240 3456 (office hours only)

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Type of product : Mixture

Classification (REGULATION (EC) No 1272/2008)

Eye irritation, Category 2 H319: Causes serious eye irritation.

2.2 Label elements

Labelling (REGULATION (EC) No 1272/2008)

Hazard pictograms :

Signal word : Warning

Hazard statements : H319 Causes serious eye irritation.

Precautionary statements : **Prevention**:

P264 Wash skin thoroughly after handling.

P280 Wear protective gloves/ eye protection/ face

protection.

according to Regulation (EC) No. 1907/2006

Everbuild Glass Cleaner Revision Date 30.01.2018







Print Date 31.01.2018

Response:

P305 + P351 + P338 IF IN EYES: Rinse cautiously with wa-

ter for several minutes. Remove contact lenses, if present and easy to do. Continue

rinsing.

Version 1.0

P337 + P313 If eye irritation persists: Get medical advice/

attention.

2.3 Other hazards

This substance/mixture contains no components considered to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of 0.1% or higher.

SECTION 3: Composition/information on ingredients

3.2 Mixtures

Hazardous components

Chemical name CAS-No. EC-No. Registration number	Classification (REGULATION (EC) No 1272/2008)	Concentration [%]
isopropanol 67-63-0 200-661-7 01-2119457558-25-XXXX	Flam. Liq.2; H225 Eye Irrit.2; H319 STOT SE3; H336	>= 10 - < 20
2-butoxyethanol 111-76-2 203-905-0 01-2119475108-36-XXXX	Acute Tox.4; H332 Acute Tox.4; H312 Acute Tox.4; H302 Eye Irrit.2; H319 Skin Irrit.2; H315	>= 1 - < 2,5

For the full text of the H-Statements mentioned in this Section, see Section 16.

SECTION 4: First aid measures

4.1 Description of first aid measures

General advice : Move out of dangerous area.

Consult a physician.

Show this safety data sheet to the doctor in attendance.

If inhaled : Move to fresh air.

Consult a physician after significant exposure.

In case of skin contact : Take off contaminated clothing and shoes immediately.

Wash off with soap and plenty of water. If symptoms persist, call a physician.

In case of eye contact : Immediately flush eye(s) with plenty of water.

Remove contact lenses.

according to Regulation (EC) No. 1907/2006

Everbuild Glass Cleaner



Keep eye wide open while rinsing.

If eye irritation persists, consult a specialist.

If swallowed : Do not induce vomiting without medical advice.

Rinse mouth with water.

Do not give milk or alcoholic beverages.

Never give anything by mouth to an unconscious person.

BUILDING TRUST

4.2 Most important symptoms and effects, both acute and delayed

Symptoms : Excessive lachrymation

See Section 11 for more detailed information on health effects

and symptoms.

Risks : irritant effects

Causes serious eye irritation.

4.3 Indication of any immediate medical attention and special treatment needed

Treatment : Treat symptomatically.

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media : Use extinguishing measures that are appropriate to local cir-

cumstances and the surrounding environment.

5.2 Special hazards arising from the substance or mixture

Hazardous combustion prod-

ucts

: No hazardous combustion products are known

5.3 Advice for firefighters

for firefighters

Special protective equipment : In the event of fire, wear self-contained breathing apparatus.

Further information : Standard procedure for chemical fires.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

Personal precautions : Use personal protective equipment.

Deny access to unprotected persons.

6.2 Environmental precautions

6.3 Methods and materials for containment and cleaning up

according to Regulation (EC) No. 1907/2006

Everbuild Glass Cleaner







Version 1.0 Print Date 31.01.2018

Methods for cleaning up : Soak up with inert absorbent material (e.g. sand, silica gel,

acid binder, universal binder, sawdust).

Keep in suitable, closed containers for disposal.

6.4 Reference to other sections

For personal protection see section 8.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

Advice on safe handling : Avoid exceeding the given occupational exposure limits (see

section 8). Do not get in eyes, on skin, or on clothing. For personal protection see section 8. Smoking, eating and drinking should be prohibited in the application area. Follow standard hygiene measures when handling chemical products

Advice on protection against

fire and explosion

: Normal measures for preventive fire protection.

Hygiene measures : Handle in accordance with good industrial hygiene and safety

practice. When using do not eat or drink. When using do not smoke. Wash hands before breaks and at the end of workday.

7.2 Conditions for safe storage, including any incompatibilities

Requirements for storage areas and containers

: Keep container tightly closed in a dry and well-ventilated place. Containers which are opened must be carefully resealed and kept upright to prevent leakage. Store in accord-

ance with local regulations.

Other data : No decomposition if stored and applied as directed.

7.3 Specific end use(s)

Specific use(s) : Consult most current local Product Data Sheet prior to any

use.

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Components with workplace control parameters

Components	CAS-No.	Value	Control parame-	Basis *
			ters *	
isopropanol	67-63-0	TWA	400 ppm	GB EH40
			999 mg/m3	
		STEL	500 ppm	GB EH40
			1.250 mg/m3	
2-butoxyethanol	111-76-2	TWA	25 ppm	GB EH40
		STEL	50 ppm	GB EH40

according to Regulation (EC) No. 1907/2006

Everbuild Glass Cleaner





TWA	20 ppm 98 mg/m3	2000/39/EC
STEL	50 ppm	2000/39/EC
	246 mg/m3	

Biological occupational exposure limits

Substance name	CAS-No.	Control parameters	Sampling time	Basis
2-butoxyethanol		butoxyacetic acid: 240Millimoles per mole Creatinine (Urine)	After shift	GB EH40 BAT

8.2 Exposure controls

Personal protective equipment

Eye protection : Safety glasses with side-shields

Eye wash bottle with pure water

Hand protection : Chemical-resistant, impervious gloves complying with an ap-

proved standard must be worn at all times when handling chemical products. Reference number EN 374. Follow manu-

facturer specifications.

Suitable for short time use or protection against splashes:

Butyl rubber/nitrile rubber gloves (0,4 mm), Contaminated gloves should be removed.

Suitable for permanent exposure:

Viton gloves (0.4 mm), breakthrough time >30 min.

Skin and body protection : Protective clothing (e.g. Safety shoes acc. to EN ISO 20345,

long-sleeved working clothing, long trousers). Rubber aprons and protective boots are additionally recommended for mixing

and stirring work.

Respiratory protection : Respirator selection must be based on known or anticipated

exposure levels, the hazards of the product and the safe work-

ing limits of the selected respirator.

organic vapor filter (Type A)

A1: < 1000 ppm; A2: < 5000 ppm; A3: < 10000 ppm Ensure adequate ventilation. This can be achieved by local exhaust extraction or by general ventilation. (EN 689 - Methods for determining inhalation exposure). This applies in particular to the mixing / stirring area. In case this is not sufficent to keep the concentrations under the occupational exposure limits then respiration protection measures must be used.

according to Regulation (EC) No. 1907/2006

Everbuild Glass Cleaner Revision Date 30.01.2018





Version 1.0 Print Date 31.01.2018

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Appearance : liquid

Colour : colourless

Odour : sweet

Odour Threshold : No data available

Flash point : > 61 °C

Autoignition temperature : No data available

Decomposition temperature : No data available

Lower explosion limit (Vol-%) : No data available

Upper explosion limit (Vol-%) : No data available

Flammability : No data available

Explosive properties : No data available

Oxidizing properties : No data available

pH : No data available

Melting point/range / Freez-

Boiling point/boiling range

Vapour pressure

ing point

No data availableNo data available

Density : ca.0,97 g/cm3

at 20 °C

: 42,9963 hPa

Water solubility : soluble

Partition coefficient: n-

octanol/water

: No data available

Viscosity, dynamic : No data available

Viscosity, kinematic : > 7 mm2/s

at 40 °C

Relative vapour density : No data available

Evaporation rate : No data available

according to Regulation (EC) No. 1907/2006

Everbuild Glass Cleaner Revision Date 30.01.2018



Version 1.0

9.2 Other information

No data available

SECTION 10: Stability and reactivity

10.1 Reactivity

No dangerous reaction known under conditions of normal use.

10.2 Chemical stability

The product is chemically stable.

10.3 Possibility of hazardous reactions

Hazardous reactions : Stable under recommended storage conditions.

10.4 Conditions to avoid

Conditions to avoid : No data available

10.5 Incompatible materials

Materials to avoid : No data available

10.6 Hazardous decomposition products

Hazardous decomposition

products No decomposition if stored and applied as directed.

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Acute toxicity

Not classified based on available information.

Components:

isopropanol:

Acute oral toxicity : LD50 Oral (Rat): < 5.000 mg/kg

Acute inhalation toxicity : LC50 (Rat): > 20 mg/l

Exposure time: 4 h
Test atmosphere: vapour

Acute dermal toxicity : LD50 Dermal (Rabbit): > 5.000 mg/kg

Skin corrosion/irritation

Not classified based on available information.

Serious eye damage/eye irritation

Causes serious eye irritation.

according to Regulation (EC) No. 1907/2006

Everbuild Glass Cleaner Revision Date 30.01.2018

the substitute Classes Classes and





Print Date 31.01.2018

Version 1.0

Respiratory or skin sensitisation

Skin sensitisation: Not classified based on available information. Respiratory sensitisation: Not classified based on available information.

Germ cell mutagenicity

Not classified based on available information.

Carcinogenicity

Not classified based on available information.

Reproductive toxicity

Not classified based on available information.

STOT - single exposure

Not classified based on available information.

STOT - repeated exposure

Not classified based on available information.

Aspiration toxicity

Not classified based on available information.

SECTION 12: Ecological information

12.1 Toxicity

No data available

12.2 Persistence and degradability

No data available

12.3 Bioaccumulative potential

No data available

12.4 Mobility in soil

No data available

12.5 Results of PBT and vPvB assessment

Product:

Assessment : This substance/mixture contains no components considered

to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of

0.1% or higher.

12.6 Other adverse effects

Product:

Additional ecological infor-

mation

: There is no data available for this product.

according to Regulation (EC) No. 1907/2006

Everbuild Glass Cleaner

Revision Date 30.01.2018





Print Date 31.01.2018

SECTION 13: Disposal considerations

13.1 Waste treatment methods

Product : The generation of waste should be avoided or minimized

wherever possible.

Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe

way.

Dispose of surplus and non-recyclable products via a licensed

waste disposal contractor.

Disposal of this product, solutions and any by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any regional

local authority requirements.

Avoid dispersal of spilled material and runoff and contact with

soil, waterways, drains and sewers.

Version 1.0

Contaminated packaging : 15 01 10* packaging containing residues of or contaminated

by dangerous substances

SECTION 14: Transport information

14.1 UN number

Not regulated as a dangerous good

14.2 UN proper shipping name

Not regulated as a dangerous good

14.3 Transport hazard class(es)

Not regulated as a dangerous good

14.4 Packing group

Not regulated as a dangerous good

14.5 Environmental hazards

Not regulated as a dangerous good

14.6 Special precautions for user

No data available

14.7 Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable

according to Regulation (EC) No. 1907/2006

Everbuild Glass Cleaner Revision Date 30.01.2018

Trankrild Class Classian





Version 1.0

Print Date 31.01.2018

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

Prohibition/Restriction

 $\ensuremath{\mathsf{REACH}}$ - Restrictions on the manufacture, placing on

the market and use of certain dangerous substances,

preparations and articles (Annex XVII)

REACH - Candidate List of Substances of Very High

Concern for Authorisation (Article 59).

: None of the components are listed

(=> 0.1 %).

: Not applicable

: Not applicable

REACH - List of substances subject to authorisation

(Annex XIV)

REACH Information:

All substances contained in our Products are

- preregistered or registered by our upstream suppliers, and/or

preregistered or registered by us, and/orexcluded from the regulation, and/or

- exempted from the registration.

Seveso III: Directive 2012/18/EU of the European Parliament and of the Council on the control of major-accident hazards involving dangerous substances.

Not applicable

VOC-CH (VOCV) : 11 %

VOC-EU (solvent) : 11 %

If other regulatory information applies that is not already provided elsewhere in the Safety Data Sheet, then it is described in this subsection.

Health, safety and environmental regulation/legislation specific for the substance or mixture: : Environmental Protection Act 1990 & Subsidiary Regulations Health and Safety at Work Act 1974 & Subsidiary Regulations Control of Substances Hazardous to Health Regulations

(COSHH)

May be subject to the Control of Major Accident Hazards

Regulations (COMAH), and amendments.

Other regulations : Take note of Directive 92/85/EEC regarding maternity protec-

tion or stricter national regulations, where applicable.

15.2 Chemical safety assessment

No Chemical Safety Assessment has been carried out for this mixture by the supplier.

SECTION 16: Other information

Full text of H-Statements

Country GB 100000011680

10 / 11

according to Regulation (EC) No. 1907/2006

Everbuild Glass Cleaner Revision Date 30.01.2018





14 1 4 0	D: (D (04 04 0040
Version 1.0	Print Date 31.01.2018

H225	Highly flammable liquid and vapour.
H302	Harmful if swallowed.
H312	Harmful in contact with skin.
H315	Causes skin irritation.
H319	Causes serious eye irritation.
⊔ 222	Harmful if inhaled

H332 Harmful if inhaled.
H336 May cause drowsiness or dizziness.

Full text of other abbreviations

Acute Tox. Acute toxicity
Eye Irrit. Eye irritation
Flam. Liq. Flammable liquids
Skin Irrit. Skin irritation

STOT SE Specific target organ toxicity - single exposure

ADR Accord européen relatif au transport international des marchandises

Dangereuses par Route

CAS Chemical Abstracts Service
DNEL Derived no-effect level

EC50 Half maximal effective concentration

GHS Globally Harmonized System

IATA International Air Transport Association

IMDG International Maritime Code for Dangerous Goods

LD50 Median lethal dosis (the amount of a material, given all at once, which

causes the death of 50% (one half) of a group of test animals)

LC50 Median lethal concentration (concentrations of the chemical in air that

kills 50% of the test animals during the observation period)

MARPOL International Convention for the Prevention of Pollution from Ships,

1973 as modified by the Protocol of 1978

OEL Occupational Exposure Limit

PBT Persistent, bioaccumulative and toxic PNEC Predicted no effect concentration

REACH Regulation (EC) No 1907/2006 of the European Parliament and of the

Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a

European Chemicals Agency

SVHC Substances of Very High Concern

vPvB Very persistent and very bioaccumulative

Classification of the mixture:

Classification procedure:

Eye Irrit. 2 H319 Calculation method

The information contained in this Safety Data Sheet corresponds to our level of knowledge at the time of publication. All warranties are excluded. Our most current General Sales Conditions shall apply. Please consult the product data sheet prior to any use and processing.

Changes as compared to previous version!