

Halogen High Voltage DE



7786R 1000W R7s 230V 1CT

The high, constant light output and consistent color temperature of these double ended high voltage halogen lamps ensure attractive, accurately exposed pictures for both film and video. In addition, the wide choice of dimensions and power ratings opens new levels of creative freedom for the luminaire designer.

Product data

• General Characteristics

Philips Code	7786R
ANSI Code	-
LIF Code	P2/20
Cap-Base	R7s
Bulb Finish	Clear
Filament Shape	Single Coil
Operating Position	p15
Main Application	Entertainment
Life to 50% failures	300 hr

• Light Technical Characteristics

Color Temperature	3200 K
Technical	
Luminous Flux Lamp	30000 Lm

• Electrical Characteristics

Lamp Wattage	1000 W
Voltage	230 V
Dimmable	Yes
Rapid Acting HBC	6.3 V
Fuse	

• Luminaire Design Requirements

Pinch Temperature	400 (max) C
-------------------	-------------

• Product Dimensions


Base Face to Base	114.2 mm
Face A	
Overall Length C	117.5 (max) mm
Diameter D	11 (max) mm
Filament Length W	60 mm

• Product Data

Order code	923884943201
Full product code	923884943201
Full product name	7786R 1000W R7s 230V 1CT
Order product name	7786R 1000W R7s 230V 1CT/10
Pieces per pack	1
Packing configuration	10
Packs per outerbox	10
Bar code on pack - EAN1	8711500492128
Bar code on outerbox - EAN3	8711500521910
Logistic code(s) - 12NC	923884943201
Net weight per piece	0.010 kg


PHILIPS

Dimensional drawing



7786R 1000W R7s 230V 1CT

Product	A (Min)	A (Norm)	A (Max)	C (Max)	D (Max)	W (Norm)
7786R 1000W R7s 230V	-	114.2	-	117.5	11	60



R7s



© 2014 Koninklijke Philips N.V. (Royal Philips)
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2014, April 11
data subject to change