


Pressure sensor with display

PN-400-SEN14-QFRKG/USI / V



- 1 alphanumeric display 4-digit red/green
 2 LEDs Display unit / switching status
 3 programming button
 4 upper part of the housing can be rotated 345°



Product characteristics

| | | | |
|--------------------|---|--------------|------------|
| Output signal | switching signal; IO-Link; (configurable) | | |
| Measuring range | 0...400 bar | 0...5800 psi | 0...40 MPa |
| Process connection | threaded connection 1/4 NPT internal thread | | |

Application

| | | | |
|--|-----------------------------|-----------|---------|
| Special feature | Gold-plated contacts | | |
| Measuring element | metallic thin film cell | | |
| Application | for industrial applications | | |
| Media | liquids and gases | | |
| Medium temperature [°C] | -25...80 | | |
| Pressure rating | 800 bar | 11580 psi | 80 MPa |
| Min. bursting pressure | 1700 bar | 24650 psi | 170 MPa |
| Type of pressure | relative pressure | | |
| MAWP (for applications according to CRN) | 800 bar | 11580 psi | 80 MPa |

PN7270



Pressure sensor with display

PN-400-SEN14-QFRKG/USI / V

| Electrical data | | | |
|---|-----------------|---|---------------|
| Operating voltage | [V] | 18...30 DC; (according to EN 50178 SELV/PELV) | |
| Current consumption | [mA] | < 35 | |
| Min. insulation resistance | [MΩ] | 100; (500 V DC) | |
| Protection class | | III | |
| Reverse polarity protection | | yes | |
| Power-on delay time | [s] | 0.3 | |
| Integrated watchdog | | yes | |
| Inputs / outputs | | | |
| Number of inputs and outputs | | Number of digital outputs: 2 | |
| Outputs | | | |
| Total number of outputs | | 2 | |
| Output signal | | switching signal; IO-Link; (configurable) | |
| Electrical design | | PNP/NPN | |
| Number of digital outputs | | 2 | |
| Output function | | normally open / normally closed; (parameterisable) | |
| Max. voltage drop switching output DC | [V] | 2.5 | |
| Permanent current rating of switching output DC | [mA] | 150; (200 (...60 °C) 250 (...40 °C)) | |
| Switching frequency DC | [Hz] | < 170 | |
| Short-circuit protection | | yes | |
| Type of short-circuit protection | | pulsed | |
| Overload protection | | yes | |
| Measuring/setting range | | | |
| Measuring range | | 0...400 bar | 0...5800 psi |
| | | | 0...40 MPa |
| Factory setting / CMPT = 2 | | | |
| Set point SP | | 4...400 bar | 40...5800 psi |
| Reset point rP | | 2...398 bar | 20...5780 psi |
| Min. difference between SP and rP | | 2 bar | 10 psi |
| In steps of | | 2 bar | 20 psi |
| 0.2 MPa | | | |
| Status_B High Resolution / CMPT = 3 | | | |
| Set point SP | | 3...400 bar | 49...5802 psi |
| Reset point rP | | 1...398 bar | 20...5773 psi |
| Min. difference between SP and rP | | 2 bar | 30 psi |
| In steps of | | 1 bar | 1 psi |
| 0.1 MPa | | | |
| Accuracy / deviations | | | |
| Switch point accuracy | | < ± 0,5 | |
| | [% of the span] | | |
| Repeatability | [% of the span] | < ± 0,1; (with temperature fluctuations < 10 K) | |
| Characteristics deviation | | < ± 0,25 (BFSL) / < ± 0,5 (LS); (BFSL = Best Fit Straight Line; LS = limit value setting) | |
| | [% of the span] | | |
| Hysteresis deviation | | < ± 0,25 | |

PN7270



Pressure sensor with display

PN-400-SEN14-QFRKG/USI / V

| [% of the span] | | |
|-------------------------------------|--|--|
| Long-term stability | | < ± 0,05; (per 6 months) |
| | [% of the span] | |
| Temperature coefficient zero point | | 0,2; (-25...80 °C) |
| | [% of the span / 10 K] | |
| Temperature coefficient span | | 0,2; (-25...80 °C) |
| | [% of the span / 10 K] | |
| Response times | | |
| Response time | [ms] | < 3 |
| Delay time programmable dS, dr | [s] | 0...50 |
| Software / programming | | |
| Parameter setting options | | hysteresis / window; normally open / normally closed; switching logic; switch-on/switch-off delay; Damping; Display unit |
| Interfaces | | |
| Communication interface | | IO-Link |
| Transmission type | | COM2 (38,4 kBaud) |
| IO-Link revision | | 1.1 |
| SDCI standard | | IEC 61131-9 |
| SIO mode | | yes |
| Required master port type | | A; (when pin 2 not connected: B) |
| | Type of operation | DeviceID |
| Supported DeviceIDs | Factory setting / CMPT = 2 | 450 d / 00 01 c2 h |
| | Status_B High Resolution / CMPT = 3 | 627 d / 00 02 73 h |
| Note | For further information please see the IODD PDF file at "Downloads" | |
| Factory setting / CMPT = 2 | | |
| Profiles | Smart Sensor: Process Data Variable; Device Identification, Device Diagnosis | |
| Min. process cycle time | [ms] | 2.3 |
| IO-Link resolution pressure | [bar] | 1 |
| IO-Link resolution pressure | [MPa] | 0.1 |
| | function | bit length |
| IO-Link functions (cyclical) | pressure | 14 |
| | binary switching information | 2 |
| IO-Link functions (acyclical) | application specific tag | |
| Status_B High Resolution / CMPT = 3 | | |
| Profiles | Smart Sensor ED2: Digital Measuring Sensor (0x000A), Identification and Diagnosis (0x4000) | |
| Min. process cycle time | [ms] | 3 |
| IO-Link resolution pressure | [bar] | 0.2 |
| IO-Link resolution pressure | [MPa] | 0.02 |
| | function | bit length |
| IO-Link functions (cyclical) | pressure | 16 |
| | device status | 4 |
| | binary switching information | 2 |
| IO-Link functions (acyclical) | application specific tag | |

PN7270



Pressure sensor with display


PN-400-SEN14-QFRKG/USI /V

| Operating conditions | | |
|---|---|--|
| Ambient temperature | [°C] | -25...80 |
| Storage temperature | [°C] | -40...100 |
| Protection | | IP 65; IP 67 |
| Tests / approvals | | |
| EMC | | DIN EN 61000-6-2 DIN EN 61000-6-3 |
| Shock resistance | | DIN EN 60068-2-27 50 g (11 ms) |
| Vibration resistance | | DIN EN 60068-2-6 20 g (10...2000 Hz) |
| MTTF | [years] | 214 |
| UL approval | | UL Approval no. J003 |
| Pressure Equipment Directive | | Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request |
| Mechanical data | | |
| Weight | [g] | 219 |
| Materials | | 1.4542 (17-4 PH / 630); stainless steel (1.4404 / 316L); PBT+PC-GF30; PBT-GF20; PC |
| Materials (wetted parts) | | 1.4542 (17-4 PH / 630) |
| Min. pressure cycles | | 100 million |
| Process connection | | threaded connection 1/4 NPT internal thread |
| Restrictor element integrated | | no (can be retrofitted) |
| Displays / operating elements | | |
| Display | Display unit switching status measured values | 3 x LED, green (bar, psi, MPa) 2 x LED, yellow alphanumeric display, red/green 4-digit |
| Remarks | | |
| Pack quantity | | 1 pcs. |
| Electrical connection | | |
| Connector: 1 x M12; Contacts: gold-plated | | |
|  | | |

Pressure sensor with display

PN-400-SEN14-QFRKG/USI /V

Connection



| | |
|------|---|
| OUT1 | switching output IO-Link |
| OUT2 | switching output colours to DIN EN 60947-5-2 Core colours : |
| BK = | black |
| BN = | brown |
| BU = | blue |
| WH = | white |