

ITEM	MOLEX P/N	DESCRIPTION	QTY	UOM
A	39014041	MiniFit Jr Rec Hsg SR V-0 4Ckt	1	PC
B	39000077	MiniFit Term Crp Fem Chn Bs Tin 16awg	4	PC
C	--	RESIN TPE NAT SANTOPRENE	A/R	KG
D	--	MOLD PART INNER CAP	2	PC
E	--	MASTER BATCH BLACK COLOR	A/R	KG
F	--	RESIN PP RTP 151 A NAT UL94V-0 HF	A/R	KG

FROM	TO	CABLE DESCRIPTION	COLOR
A1	--	4CX16AWG UNSHD BK UL2464	BLACK
A2	--		RED
A3	--		WHITE
A4	--		GREEN




TABLE		
PART NUMBER	TITLE	L1
2171590405	4 CKT OVERMOLD MINIFIT JR PIGTAIL 500MM	500±10
2171590410	4 CKT OVERMOLD MINIFIT JR PIGTAIL 1M	1000±20
2171590420	4 CKT OVERMOLD MINIFIT JR PIGTAIL 2M	2000±25
2171590430	4 CKT OVERMOLD MINIFIT JR PIGTAIL 3M	3000±30

NOTES:

- MOLDING MATERIAL:
  - INNERCAP: PA66 NYLON RESIN.
  - OVERMOLD: SANTOPRENE TPE RESIN & MASTER BATCH BLACK
  - INNERMOLD: PP NAT UL94V-0
- ELECTRICAL PERFORMANCE:
  - VOLTAGE RATING: 300V AC.
  - THIS PRODUCT MUST PASS 100% CONTINUITY TEST PER MOLEX ES-36586-004.
    - DIELECTRONIC STRENGTH: 500V DC/0.01 SEC.
    - INSULATION RESISTANCE: 20M OHMS
- CONNECTOR VIEWS ARE SHOWN FROM MATING SIDE.
- MECHANICAL PERFORMANCE:
  - CABLE HARNESS SHOULD WITHSTAND AN AXIAL FORCE OF 5KGF FOR ONE MINUTE BETWEEN OVERMOLD AND CONNECTOR WITHOUT PHYSICAL DAMAGE.
  - OVERMOLD SIDE CAN PASS THE BENDING TEST IN 100 CYCLES AT EACH OF 2 PLANES, PER EIA364-41 CONDITION I.

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	CURRENT REV DESC:		<b>molex</b>																												
	<table border="1"> <tr> <th>DIMENSION UNITS</th> <th>SCALE</th> </tr> <tr> <td>mm</td> <td>NTS</td> </tr> </table>	DIMENSION UNITS	SCALE		mm	NTS	<table border="1"> <tr> <th>GENERAL TOLERANCES (UNLESS SPECIFIED)</th> <th>ANGULAR TOL</th> </tr> <tr> <td>4 PLACES ±</td> <td>± °</td> </tr> <tr> <td>3 PLACES ±</td> <td></td> </tr> <tr> <td>2 PLACES ±</td> <td></td> </tr> <tr> <td>1 PLACE ±</td> <td></td> </tr> <tr> <td>0 PLACES ±</td> <td></td> </tr> </table>		GENERAL TOLERANCES (UNLESS SPECIFIED)	ANGULAR TOL	4 PLACES ±	± °	3 PLACES ±		2 PLACES ±		1 PLACE ±		0 PLACES ±		<table border="1"> <tr> <td>EC NO: 670688</td> <td>2021/07/16</td> </tr> <tr> <td>DRWN: SBS04</td> <td>2021/07/19</td> </tr> <tr> <td>CHK'D: RDESAI01</td> <td>2021/07/19</td> </tr> <tr> <td>APPR: RDESAI01</td> <td>2021/07/19</td> </tr> </table>		EC NO: 670688	2021/07/16	DRWN: SBS04	2021/07/19	CHK'D: RDESAI01	2021/07/19	APPR: RDESAI01	2021/07/19	SEE TABLE	
DIMENSION UNITS	SCALE																															
mm	NTS																															
GENERAL TOLERANCES (UNLESS SPECIFIED)	ANGULAR TOL																															
4 PLACES ±	± °																															
3 PLACES ±																																
2 PLACES ±																																
1 PLACE ±																																
0 PLACES ±																																
EC NO: 670688	2021/07/16																															
DRWN: SBS04	2021/07/19																															
CHK'D: RDESAI01	2021/07/19																															
APPR: RDESAI01	2021/07/19																															
DIVISIONAL SYMBOLS	<table border="1"> <tr> <th>INITIAL REVISION:</th> <th>DOCUMENT NUMBER</th> <th>DOC TYPE</th> <th>DOC PART</th> <th>REVISION</th> </tr> <tr> <td>DRWN: SBS04</td> <td>2171590405</td> <td>PSD</td> <td>000</td> <td>B1</td> </tr> <tr> <td>APPR: MNARAYAN01</td> <td>2021/05/10</td> <td></td> <td></td> <td></td> </tr> </table>	INITIAL REVISION:	DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION	DRWN: SBS04	2171590405	PSD	000	B1	APPR: MNARAYAN01	2021/05/10				<table border="1"> <tr> <th>DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</th> <th>THIRD ANGLE PROJECTION</th> <th>DRAWING</th> <th>SERIES</th> <th>MATERIAL NUMBER</th> <th>CUSTOMER</th> <th>SHEET NUMBER</th> </tr> <tr> <td></td> <td></td> <td>A3-SIZE</td> <td>217159</td> <td>SEE TABLE</td> <td>GENERAL MARKET</td> <td>1 OF 1</td> </tr> </table>		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER			A3-SIZE	217159	SEE TABLE	GENERAL MARKET	1 OF 1
INITIAL REVISION:	DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION																												
DRWN: SBS04	2171590405	PSD	000	B1																												
APPR: MNARAYAN01	2021/05/10																															
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER																										
		A3-SIZE	217159	SEE TABLE	GENERAL MARKET	1 OF 1																										