

ACMS-Q4523F

Request Samples



Check Inventory (>)



4.5 x 3.2 x 2.3 mm **RoHS/RoHS II Compliant** MSL Level = 1

Features

- AEC-Q200 compliant, Grade 1
- PPAP ready and supported
- Manufactured in TS/IATF 16949 production lines
- Excellent impedance characteristics

Applications

- Differential signal line common mode noise suppression.
- Multimedia devices
- Automotive applications such as ADAS, Infotainment, Sensing, TCU
- Automotive CANFD

Electrical Specifications

Part Number	Inductance (μH) (+50%/-30%)	DCR (mΩ)	Rated Current (A)	Rated Voltage (Vdc)	Insulation Resistance $(M\Omega)$
		Max	Max	Max	Min
ACMS-Q4523F-101	100	2000	0.2	50	10

Rated Current is based on an Irms temperature rise of 20°C

Inductance Test Conditions: 0.1MHz/0.1V

ACMS-O4523F is AEC-O200 Automotive certified

ACMS-O4523F Series is RoHS Compliant and Pb free

Operating Temperature: -40°C to +150°C (Including self-heating)

Storage Temperature (on PCB): -40°C to +150°C Storage (in original packaging): <40°C, <70% RH





ACMS-Q4523F

Request Samples (>)




Check Inventory (>)



4.5 x 3.2 x 2.3 mm **RoHS/RoHS II Compliant** MSL Level = 1

Electrical Specifications







ACMS-Q4523F

Request Samples (>)





Check Inventory (>)




4.5 x 3.2 x 2.3 mm RoHS/RoHS II Compliant MSL Level = 1

Mechanical Specifications





A	В	C	D	E
4.5 ± 0.2	3.2 ± 0.2	2.3 ± 0.2	1.0 ± 0.1	1.25 ± 0.1



Recommended Layout

Dimensions: mm





ACMS-Q4523F

Request Samples (>)




Check Inventory (>)




4.5 x 3.2 x 2.3 mm **RoHS/RoHS II Compliant** MSL Level = 1

Schematic




Materials



	Description	Specification
a	Upper Plate	Ni-Zn Ferrite
b	Core	Ni-Zn Ferrite
c	Wire	Enameled copper wire
d	Electrode	Ag/Ni/Sn

Part Identification







ACMS-Q4523F

Request Samples (>)




Check Inventory (>)



4.5 x 3.2 x 2.3 mm RoHS/RoHS II Compliant MSL Level = 1

Reflow Profile



Zone	Description	Temperature	Times
1	Preheat	$T_{SMIN} \sim T_{SMAX} \\ 150^{\circ}C \sim 200^{\circ}C$	$60 \sim 120 \text{ sec.}$
2	Reflow	T _L 220°C	60 ~ 90 sec.
3	Peak heat	T _P 260°C Max	10 sec. MAX





ACMS-Q4523F

Request Samples




Check Inventory (>)




4.5 x 3.2 x 2.3 mm **RoHS/RoHS II Compliant** MSL Level = 1

Packaging

Tape & Reel: 2000pcs/reel



Series	A	В	C	D
ACMS-Q4523F	13.0 ± 0.5	100.0 ± 2.0	13.0 ± 0.5	330



A	В	P	K	T
3.51	4.82	8.0	3.05	0.35
±0.10	± 0.10	± 0.10	± 0.10	± 0.05

Dimensions: mm

ATTENTION: Abracon LLC's products are COTS - Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.

