# Cylindrical Fuses 10mm × 38mm







#### **Features**

Rated Voltage: 1100V DCRated Current: 1A to 32A

• Breaking Capacity: 30 kA at 1100V DC(1A to 20A)--UL

30 kA at 1100V DC(1A to 32A)--IEC

Time Constant: 1ms to 3ms

10mm × 38mm PV fuse link with glass-fiber

· Special design with silver plated caps for high-power PV applications

Approvals: UL 248-19Approvals: IEC 60269-6

## **Electrical Specifications**

Part Number	Rated Current	Ampere Code	Breaking Capacity	I²t (A²s)		Dissipation(W)		Certifications
				Pre-Arcing	Total	80% In	100% In	UL
MP008149	10A	2100	30 kA@ 1100 V DC	200	1100	1.1	1.4	
MP008150	12A	2120		240	1320	1.3	1.7	
MP008151	2A	1200		40	220	0.2	0.3	
MP008152	4A	1400		80	440	0.4	0.6	•
MP008153	1A	1100		20	110	0.1	0.1	
MP008154	6A	1600		120	660	0.6	0.9	
MP008155	8A	1800		160	880	0.9	1.1	


#### Note:

- (1) DC cold resistances are measured at <10 % of rated current in ambient temperature of 25 ±5°C
- (2) Typical pre-arcing I2t measured at 10\*In current

#### **Time VS Current Characteristics Table**

Rated Current	100%	135%	200%	100%	113%	145%
1-32 A	Temperature Stabilization	<1 h	<4 min	Temperature Stabilization	>1 h	<1 h

### Diagram



Dimensions: Millimetres

### **Applications**

- PV combiner/ junction boxes
- Inverters
- · Battery Charge Controllers


Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro



# Cylindrical Fuses 10mm × 38mm



## Time Current Curve (reference)



#### **Part Number Table**

Description	Part Number
Cylindrical Fuse, 10mm × 38mm, 10A, 1100V DC	MP008149
Cylindrical Fuse, 10mm × 38mm, 12A, 1100V DC	MP008150
Cylindrical Fuse, 10mm × 38mm, 2A, 1100V DC	MP008151
Cylindrical Fuse, 10mm × 38mm, 4A, 1100V DC	MP008152
Cylindrical Fuse, 10mm × 38mm, 10A, 1100V DC	MP008153
Cylindrical Fuse, 10mm × 38mm, 6A, 1100V DC	MP008154
Cylindrical Fuse, 10mm × 38mm, 8A, 1100V DC	MP008155

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

