
## **Features**

- Low in height, suitable for thin equipment
- Ceramic package and metal lid assures high reliability
- Tight tolerance and stability available

## **Applications**

- High density applications
- Modem, communication and test equipment
- PMCIA, wireless applications
- Automotive applications






General Specifications				
Frequency Range	10.000 to 60.000MHz (Fundamental)			
Frenquency Tolerance at 25°C	±10 to ±100ppm (±30ppm standard)			
Frequency Stability over Temperature Range	See Stability vs. Temperature Table			
Storage Temperature	-55 to +125°C			
Load Capacitance C <sub>L</sub>	7 to 32pF and Series Resonance			
Shunt Capacitance C <sub>0</sub>	5.0pF max.			
Equivalent Series Resistance (ESR)	See ESR Table			
Drive Level	100μW max.			
Aging per Year	±3ppm max.			
Insulation Resistance (M $\Omega$ )	500 at 100Vdc ±15Vdc			

Equivalent Series Resistance (ESR)				
Frequency Range - MHz	$\Omega$ max.	Mode of Operation		
10.000 to 20.000	100	Fundamental		
20.100 to 25.000	80			
25.100 to 60.000	60			

Frequency Stability vs. Temperature						
Operating Temperature	±10ppm	±20ppm	±30ppm	±50ppm	±100ppm	
-20 to +70°C	0	0	0	0	0	
-40 to +85°C	O*	0	•	0	0	
-40 to +105°C	-	-	-	0	0	
-40 to +125°C	-	-	-	-	0	
*Operating Temperature -30 to +85°C		*Operating Temperature -30 to +85°C • standard • availab				




Part Numbering Guide									
Qantek Code	Package	Nominal Frequency (in MHz)	Vibration Mode	Load Capacitance	Operating Tem- perature Range	Frequency Tolerance	Frequency Stability	Automotive Indicator	Packaging
Q = Qantek	C32 = 2.5x3.2 4-Pad SMD	7 digits including the decimal point (f.ie. 12.0000)	F = AT-Fund	S = Series 08 = 8pF 12 = 12pF 18 = 18pF 20 = 20pF etc.	A = -20 to +70°C B = -40 to +85°C C = -40 to +105°C D = -40 to +125°C	1 = ±10ppm 2 = ±20ppm 3 = ±30ppm 5 = ±50ppm 0 = ±100ppm	1 = ±10ppm 2 = ±20ppm 3 = ±30ppm 5 = ±50ppm 0 = ±100ppm	A = AEC-Q200	M = 250pcs Tape&Reel R = 1000pcs Tape&Reel R3 = 3000pcs Tape&Reel
Example: Q	Example: QC3212.0000F12B33R bold letters = recommended standard specification					led standard specification			



**QANTEK Technology Corporation** 

Phone: +1 877-227-0440 (tollfree) www.qantek.com Fax: +1 877-227-0440 (tollfree) info@qantek.com



## **Marking Code Guide**


Contains frequency, Qantek manufacturing code, production code (month and year) and load capacitance.

Month Codes					
January	А	July	G		
February	В	August	Н		
March	С	September	1		
April	D	October	J		
May	Е	November	K		
June	F	December	L		

Year Codes					
2010	0	2011	1	2012	2
2013	3	2014	4	2015	5

Load Capacitance Code in pF					
pF	PN Code	pF	PN Code		
12	Α	20	F		
18	В	22	G		
8	С	30	Н		
10	D	32	ı		
16	Е	S	S		

Example: First Line: 12.000 (Frequency) Second Line: QA1A (Qantek - January - 2011 - 12 pF)



Environmental Specifications				
Mechanical Shock	MIL-STD-202, Method 213, C			
Vibration	MIL-STD-202, Method 201 & 204			
Thermal Cycle	MIL-STD, Method 1010, B			
Gross Leak	MIL-STD-202, Method 112			
Fine Leak	MIL-STD-202, Method 112			

All specifications are subject to change without notice.



Phone: +1 877-227-0440 (tollfree) www.qantek.com Fax: +1 877-227-0440 (tollfree) info@qantek.com