


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO. *	BUNDLE DIA.		A	B	C	D	E	F	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	TIP STYLE	WEIGHT lbs./100 pcs. (g)
	MIN. in (mm)	MAX. in (mm)										
PLT2H	.188 (4.8)	2.00 (51)	.075 (1.9)	.300 (7.6)	.338 (8.6)	.290 (7.4)	.480 (12.2)	8.1 (206)	120 (534)	HEAVY	STRAIGHT	.76 (346)
PLT2.5H	.188 (4.8)	2.50 (64)	.075 (1.9)	.300 (7.6)	.338 (8.6)	.290 (7.4)	.480 (12.2)	9.8 (251)	120 (534)	HEAVY	STRAIGHT	.90 (408)
PLT3H	.188 (4.8)	3.00 (76)	.075 (1.9)	.300 (7.6)	.338 (8.6)	.290 (7.4)	.480 (12.2)	11.4 (290)	120 (534)	HEAVY	STRAIGHT	1.04 (472)
PLT4H	.188 (4.8)	4.00 (102)	.075 (1.9)	.300 (7.6)	.338 (8.6)	.290 (7.4)	.480 (12.2)	14.5 (368)	120 (534)	HEAVY	STRAIGHT	1.28 (581)
PLT5H	.188 (4.8)	5.00 (127)	.078 (2.0)	.350 (8.9)	.406 (10.1)	.340 (8.6)	.560 (14.2)	17.7 (450)	175 (778)	HEAVY	STRAIGHT	2.06 (934)
PLT6H	.188 (4.8)	6.00 (152)	.078 (2.0)	.350 (8.9)	.406 (10.1)	.340 (8.6)	.560 (14.2)	20.9 (530)	175 (778)	HEAVY	STRAIGHT	2.46 (1116)
PLT8H	.188 (4.8)	9.00 (229)	.078 (2.0)	.350 (8.9)	.406 (10.3)	.340 (8.6)	.560 (14.2)	30.6 (779)	175 (778)	HEAVY	STRAIGHT	3.36 (1524)
PLT13H	5.50 (140)	13.00 (330)	.078 (2.0)	.350 (8.9)	.406 (10.3)	.340 (8.6)	.560 (14.2)	43.3 (1100)	175 (778)	HEAVY	STRAIGHT	4.59 (2080)

NOTE:

\*SEE [www.panduit.com](http://www.panduit.com) FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, PART MATERIAL, PART COLOR AND ANY THIRD PARTY RECOGNITION OR COMPLIANCE.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

REV						DESCRIPTION	ECN	DRAWN BY				DATE	CHK	SCALE	DRAWING NUMBER	
10	4/04/14	BWG	MPH	JADE	UPDATED NOTES.		SS-5540/10	CEW			12-27-84	HVP	NONE		SHT 1 OF 1	
09	8/13/13	BWG	KJM	RTFI	UPDATED TITLE BORDER.		SS-5540/09								A	

TITLE		PAN-TY CABLE TIES - PLT SERIES	
ITEM REVISION NAME		CUSTOMER DRAWING	
DATASET FILE NAME		W10001CD/10	
		<b>PANDUIT</b>	
		MATERIAL: NYLON 6.6	
		DRAWING NUMBER: SS-5540 SHEET 4	
		THIRD ANGLE PROJECTION	

D10100DA/16