



Slim High Speed 4K UHD 30Hz HDMI Lead with Ethernet



Specifications

Connector Type A	: HDMI Plug
Connector Type B	: HDMI Plug
Contact Resistance	: 3Ω Max.
Insulation Resistance	: 5MΩ Min.
Hi-Pot Test	: DC 300V/10ms
Jacket Colour	: Black

Diagram



No.	Part Name	Description	Unit
1	Connector	HDMI AM 19P Pin:G/F, Shell:Gold plated	2 Pcs
2	Shell	Silver Zinc Alloy Housing	
3	Inner Molding	PE, Nature Colour	10g
4	Outer Molding	Black PVC 45P	20g
5	Cable	32AWG[(1C/0.20BC*1P+D1C/0.20BC+AL/MY)*5P+1C/0.20BC*4C]+AL+D1C/0.20BC+B64/0.12AM Black PVC jacket OD:4.5±0.2mm	-

Part Number Table

Description	Length "L" (mm)	Part Number
Slim High Speed 4K UHD 30Hz HDMI Lead with Ethernet, Male to Male, Black	500 ±20	PSG3239-HDMI-0.5
	1000 ±30	PSG3240-HDMI-1
	2000 ±30	PSG3241-HDMI-2
	3000 ±30	PSG3242-HDMI-3
	5000 ±50	PSG3243-HDMI-5

Dimensions : Millimetres

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-SIGNAL is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands
 Farnell.com/exclusive-brands
 Element14.com/exclusive-brands

