


Product information

12 11 180

Insulation Stripper

With adapted blades

- With replaceable blades for 4 (adapted to diameters) or 6 (adapted to cross-sections) different conductor cross-sections
- Leave wire undamaged thanks to precision-ground blade shapes, even multi-stranded conductors are stripped gently
- During stripping, the wire is held firmly by clamping jaws
- With length stop for constant stripping length during repetitive work
- A spring leads the stripper back to the starting position
- Blade: special tool steel, oil-hardened
- Pliers body: aluminium



MM

General	
Article No.	12 11 180
EAN	4003773000792
Pliers	black lacquered
Handles	with plastic grips
Weight	368 g
Dimensions	180 x 74 x 19 mm
Reach	no
RohS	no

Technical details	
Stripping capacities (diameter)	Ø 0.5 / 1.2 / 1.6 / 2 mm

Classification	
eCl@ss 5.1.4	21040302
ETIM 5.0	EC000163
ETIM 6.0	EC000163
proficl@ss 6.0	AAA002c003
UNSPSC 13.1	27111510

Spare Parts	
12 19 180 07	Joining bar (7) for 12 11/21 ...
12 19 180	1 pair of spare blades for 12 11 180,
12 19 180 04	Insulation support (4) for 12 11/21 ...
12 19 180 09	Screw (9) for 12 11/21 ...
12 19 180 08	Bolt (8) for 12 11/21 ...
12 19 180 06	Guide plate (6) for 12 11/21 ...
12 19 180 10	Torsion spring (10) for 12 11/21 ...

Spare Parts	
12 19 180 11	Washer (11) for 12 11/21 ..,
12 19 180 12	Joint pin (12) for 12 11/21 ..,
12 19 180 13	Opening spring (13) for 12 11/21 ..,
12 19 180 18	Spring for number 16 (18),
12 19 180 14	Joint screw (14) for 12 11/21 ..,
12 19 180 15	Handle sleeve (15) for 12 11/21 ..,
12 19 180 16	Intermediate stop lever (16) for 12 11/21 ..,
12 19 180 17	Bolt for intermediate stop lever (17) for 12 11/21 ..,
12 19 180 22	Length stop and screws (19-21) for 12 11/21 ..,
12 19 180 23	Adjusting and fastening screws (20-21) for 12 11/21 ..,

technical change and errors excepted