

## Push rod clamp

Small angular base



### Application:

For quick and secure clamping on machine tables and appliances.

### Execution:

- Compression and tension clamp with small angular base
- Individual parts galvanised
- Long push rod version
- Case-hardened and lubricated bearing bushes
- Ergonomic, oil-resistant handle with large hand rest and soft components.

### Advantage:

- Handle can be adjusted at any angle to the base surface

### Delivery:

With thrust bolt and protective cap



<b>Art. no.</b>	<b>26217 005</b>
<b>Brand</b>	AMF
<b>Manufacturer Part Number</b>	94094
<b>Hole distance</b>	16 mm
<b>Size</b>	0
<b>Bore diameter</b>	4.5 mm
<b>Clamping stroke</b>	16 mm
<b>Retaining force</b>	800 N
<b>Clamping height</b>	12 mm
<b>Width of angled base</b>	6.5 mm
<b>Length</b>	66.5 mm
<b>Height</b>	49.3 mm
<b>Thumbscrew size</b>	M4 x 20 mm
<b>Gross Weight</b>	0.076 kg
<b>Product Group</b>	260

### EAN

4020772094096