

3-point internal micrometer set

IMICRO



Application:

For high-precision measurement of through-bores, even at high measuring depths.

Execution:

- Carbide measuring faces
- Friction coupling for consistent, repeatable measuring force
- Self-centring and self-aligning

Advantage:

- Ground step taper for high precision
- Insensitive to influence of body heat from the user's hand and fluctuations in ambient temperature
- The only 3-point internal micrometer working on the Abbe principle

Delivery:

Individual devices, setting rings, measuring depth extensions from 6 mm to 12 mm, in a case



Art. no.	31714 120
Brand	TESA
Manufacturer Part Number	00811500
Min./max. length measuring range	20-40 mm
Measuring depth	150 mm
Error limit	4 µm
Digit increment	0.005 mm
Adjusting ring diameter	35 mm, 25 mm
DIN	863
Calibration Group	I
Gross Weight	2.900 kg
Product Group	362

EAN

7630041108118