


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0439382102**  
**Status:** **Active**  
**Overview:** Mini-Fit Sr. Power Connectors  
**Description:** 10.00mm Pitch Mini-Fit Sr. Plug Housing, Dual Row, Panel Mount, 8 Circuits, Black

**Documents:**

<a href="#">3D Model</a>	<a href="#">Packaging Specification PK-45286-002 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Test Summary TS-42815-001 (PDF)</a>
<a href="#">Product Specification PS-42815-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Packaging Specification PK-43938-001-001 (PDF)</a>	



Series image - Reference only

**Agency Certification**

CSA	LR19980
UL	E29179

**General**

Product Family	Crimp Housings
Series	<u>43938</u>
Application	Power, Wire-to-Wire
Overview	<u>Mini-Fit Sr. Power Connectors</u>
Product Name	Mini-Fit Sr.
UPC	800753010352

**Physical**

Circuits (maximum)	8
Color - Resin	Black
Flammability	94V-0
Gender	Plug
Glow-Wire Capable	No
Material - Resin	Polyester
Net Weight	15.538/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	Yes
Pitch - Mating Interface	10.00mm
Stackable	No
Temperature Range - Operating	-40° to +105°C

**Electrical**

Current - Maximum per Contact	50.0A
-------------------------------	-------

**Solder Process Data**

Lead-free Process Capability	N/A
------------------------------	-----

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	PK-43938-001-001, PK-45286-002
Product Specification	PS-42815-001
Sales Drawing	SD-43938-002-001, SD-43938-003-001
Test Summary	TS-42815-001

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**  
**REACH SVHC**

Not Contained Per -  
ED/61/2018 (27 June  
2018)

**Halogen-Free**  
**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

43938 Series

**Mates With**

43914

**Use With**

42817 Male Terminal and 43980 TPA Clip