


DEBUR AND BREAK SHARP EDGES

DO NOT SCALE DRAWING

REVISION



PART NO.	"A"
TRBHL-3-01	4.8
TRBHL-4-01	6.4
TRBHL-6-01	9.5
TRBHL-8-01	12.7

C	PART No. TABLE ADDED M.E. 09/07/14
B	DRG No. CHANGED M.E. 18/06/14
A	DRAWN 01/11/13

NOTES

1. MATERIAL: NYLON 66 UL-94V2;
2. COLOR: NATURAL;
3. ROHS Compliant;
4. TOP Hole: $\varnothing 4.0 \pm 0.08\text{mm}$
Panel Thickness: 1.57mm.
5. Bottom Hole: $\varnothing 7.92 \pm 0.08\text{mm}$
Panel Thickness: 6.4mm.



DESIGN RIGHT. TR FASTENINGS LTD, 2003
UNDER NO CIRCUMSTANCES MUST THIS
DRAWING BE COPIED OR DISCLOSED,
WITHOUT FIRST OBTAINING WRITTEN
AUTHORITY.

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN MILLIMETERS
SURFACE FINISH:
TOLERANCES:

NAME	DATE
DRAWN MARTIN ELLIOTT	01/11/13
CHK'D	
APP'VD	

CUSTOMER PART No

MATERIAL:

SEE NOTES

HEAT TREATMENT

N/A

FINISH:

N/A

TITLE:


BLIND HOLE LOCKING
CIRCUIT BOARD SUPPORT

DWG NO.

TRBHL-X-01

A3

PROJECTION



SHEET 1 OF 1