

Electronic micrometer

Digimatic QuickMike with disc measuring faces

Mitutoyo

Application:

For measuring tooth span on cogs, for recesses, groove distances etc.

Execution:

- measuring faces made of hardened steel
- ABS function
- HOLD (measured value storage)
- Origin (measurement presetting)
- IP65
- Non-rotating spindle

Advantage:

- Fast spindle feed
- IP65

Delivery:

Includes box, setting standard (from 25 mm), battery



Art. no.	32017 650
Brand	MITUTOYO
Manufacturer Part Number	369-421-20
Display	Digital
Min./max. length measuring range in inches	0-1.2 in
Digit increment	0.00005 in
Measuring surface diameter	20 mm
IP protection class	IP 65
Data transmission type	DIGIMATIC
Spindle clamping	No
Digit height	10 mm
Functions	Absolute function, ABS function, On/Off, Hold-function (AE lock), Origin (Dimension preset)
Min./max. measurement force	3-8 N
Error limit	0.0002 in
Number of rechargeable batteries/batteries	1 PCS
Battery designation	1,5 V SR44
DIN	863
Bracket depth	25 mm
Measuring spindle increments	10 mm
Calibration Group	D
Gross Weight	0.565 kg
Product Group	3MA

EAN

4946368736808