

## Lever gauge probe

Compact

Mitutoyo

### Application:

For measuring deviations in concentricity, axial run-out, parallelism and flatness. For centring shafts, boreholes and aligning workpieces.

### Advantage:

- Easy reading thanks to the glare-free, flat dial face

### Delivery:

Includes clamp shank, dia. 8 mm, and box



<b>Art. no.</b>	<b>32019 092</b>
<b>Brand</b>	MITUTOYO
<b>Manufacturer Part Number</b>	513-466-10E
<b>Length measuring range</b>	0.5 mm
<b>Scale value</b>	0.01 mm
<b>Measurement force</b>	0.3 N
<b>Length of measuring sensor from centre of ball</b>	18.7 mm
<b>Material of measuring ball</b>	Carbide
<b>Ball diameter</b>	2 mm
<b>Diameter</b>	29.2 mm
<b>Composition of set</b>	Lever gauge probe, un. nut, clmp. shnk. 8 mm, probe tip dia. 2 mm, carb. meas. tip
<b>Calibration Group</b>	L
<b>Gross Weight</b>	0.156 kg
<b>Product Group</b>	3MA

### EAN

4946368675626