

## wing door cabinets fitted with plastic inserts

for CNC tool carriers, SK 40, SK 50 or HSK 63

### Application:

For secure and clearly-laid-out storage and retrieval of CNC tools

### Execution:

- Sturdy sheet steel structure, lockable with grip handle and cylinder lock, including 2 keys
- With 5 pairs of guide rails, including 7 supporting profiles
- Supporting profiles are equipped with SK or HSK adapter holders (number of holders, refer to table)
- Rails are inclined (15°), can be staggered against each other and height can be adjusted in increments of 30 mm to accommodate tools of different length
- Up to 3 supporting profiles can be used per pair of rails
- Forklift-compatible base with removable base fascia for in-house transport
- cabinet can be fitted with an ELECTRONIC CODE combination lock at extra charge as an option, see no. 50392 020



<b>Art. no.</b>	<b>50658 035</b>
<b>Brand</b>	HK
<b>Manufacturer Part Number</b>	50658035
<b>Door design</b>	Full-sheet panel
<b>Equipped</b>	HSK 63
<b>Number of attachments</b>	119 pieces
<b>Height</b>	1950 mm
<b>Width</b>	1018 mm
<b>Depth</b>	620 mm
<b>Load-carrying capacity per rail pair</b>	150 kg
<b>Number of carrier sections</b>	7 PCS
<b>Load-carrying capacity per carrier section</b>	50 kg
<b>Load-carrying capacity</b>	1000 kg
<b>Central locking</b>	Yes
<b>Lock type</b>	DOM® locking system
<b>Material</b>	Sheet steel
<b>Cabinet colour</b>	Optional
<b>Colour of front</b>	Optional
<b>Surface</b>	Powder-coated
<b>Gross Weight</b>	125.000 kg
<b>Product Group</b>	507

### EAN

4053625149247