

The sub miniature ECX-34G is a compact SMD tuning fork crystal with a case ground. The $3.2 \times 1.5 \times 0.9$ mm ceramic package is ideal mobile devices, IoT and Iow noise applications.


ECX-34G SMD CRYSTAL

Request a Sample

OPERATING CONDITIONS / ELECTRICAL CHARACTERISTICS



ECX-34G SMD CRYSTAL



- Grounded Metal Cover
- 3.2 x 1.5 mm Footprint
- Low Power RTC Applications such as STM32 <u>AN2867</u>
- RoHS Compliant

DIMENSIONS (mm)




Figure 1) Top, Side, and Bottom views

PARAMETERS	CONDITIONS	ECX-34G			UNITS
		MIN	ТҮР	MAX	
Frequency			32.768		KHz
Frequency Tolerance	at +25°C			± 20	°C
Frequency Stability	-40 to +85°C	-0.028	-0.034	-0.040	ppm/°C²
Shunt Capacitance	Со		0.75		pF
Load Capacitance	Specify in P/N		12.5		рF
Drive Level				1	μW
Equivalent Series Resistance	R1			70K	Ω
Quality Factor	Q		30K		
Turnover Temperature		+20	+25	+30	°C
Operating Temperature		-40		+85	ppm
Storage Temperature		-55		+125	ppm
Aging (First Year)	@ +25°C ±3°C			±3	ppm

(2.2)

(0.08)1.4 CO. 3 #1 #2 #3 1.3 1.0 1.3(0.08)0.82 0.75 PAD CONNECTIONS 0.4 In/Out 1 22 Gnd or NC 2 0 3 Out/In

Figure 2) Suggested Land Pattern

PART NUMBERING GUIDE: Example ECS-.327-12.5-34G-TR

ECS -	FREQUENCY ABBREVIATION	LOAD CAPACITANCE	PACKAGE	CUSTOM OPTIONS Tolerance	PACKAGING
ECS	.327 = 32.768 KHz	12.5 = 12.5 pF 6 = 6 pF	34G = ECX-34G	Blank = ±20 ppm * C = ± 10 ppm	TR = Tape & Reel 3K/Reel

*Contact ECS for availability

Rev.2016





15.4

180

1.2 13.0

2


 $\phi 21$

 $\phi 13$

R1.0

φ 60

POCKET TAPE & Reel DIMENSIONS



SOLDER PROFILE				
Peak solder Temp +260°C Max 10 sec Max.				
2 Cycles Max.				
MSL 1, Lead Finish Au				




Figure 1) Suggested Reflow Profile

 $6\pm 0.$