


## Geberit PE Bogen



Beispielbild



### Verwendungszwecke

- Zur Gebäudeentwässerung
- Zur Grundstücksentwässerung

### Eigenschaften

- Beidseitig mit Elektroschweißmuffe schweißbar

### Technische Daten

Werkstoff

PE-HD

Art.-Nr.	DN	d, ø	arc	X	K	VE1	VE2	VE3	VE4
360.045.16.1	40	40 mm	45 °	4 cm	2 cm	1 St.	10 St.	100 St.	
361.045.16.1	50	50 mm	45 °	4.5 cm	2 cm	1 St.	10 St.	100 St.	
361.088.16.1	50	50 mm	88.5 °	6 cm	2 cm	1 St.	10 St.	50 St.	
363.045.16.1	56	56 mm	45 °	4.5 cm	2 cm	1 St.	10 St.	160 St.	1280 St.
363.088.16.1	56	56 mm	88.5 °	6.5 cm	2 cm	1 St.	10 St.	130 St.	
364.045.16.1	60	63 mm	45 °	5 cm	2 cm	1 St.	10 St.	260 St.	
364.088.16.1	60	63 mm	88.5 °	7 cm	2 cm	1 St.	10 St.	200 St.	
365.045.16.1	70	75 mm	45 °	5 cm	2 cm	1 St.	10 St.	50 St.	800 St.
365.088.16.1	70	75 mm	88.5 °	7.5 cm	2 cm	1 St.	10 St.	30 St.	480 St.
366.045.16.1	90	90 mm	45 °	5.5 cm	2 cm	1 St.	10 St.	30 St.	480 St.
366.088.16.1	90	90 mm	88.5 °	8 cm	2 cm	1 St.	10 St.	100 St.	
367.045.16.1	100	110 mm	45 °	6 cm	2.5 cm	1 St.	10 St.	70 St.	280 St.
367.088.16.1	100	110 mm	88.5 °	9.5 cm	2.5 cm	1 St.	10 St.	50 St.	200 St.
368.045.16.1	125	125 mm	45 °	6.5 cm	2.5 cm	1 St.	10 St.	50 St.	200 St.
368.088.16.1	125	125 mm	88.5 °	10 cm	2.5 cm	1 St.	40 St.	160 St.	
369.045.16.1	150	160 mm	45 °	6.9 cm	2 cm	1 St.	10 St.	120 St.	
369.088.16.1	150	160 mm	88.5 °	12 cm	2.5 cm	1 St.	6 St.	72 St.	
370.045.16.1	200	200 mm	45 °	18 cm	2.5 cm	1 St.	7 St.	28 St.	