

T-1 (3mm) BI-COLOR INDICATOR LAMP

P/N: L-115WEGW

HIGH EFFICIENCY RED

GREEN

Features


- •UNIFORM LIGHT OUTPUT.
- •LOW POWER CONSUMPTION.
- •3 LEADS WITH ONE COMMON LEAD.
- ●I.C. COMPATIBLE.
- •LONG LIFE SOLID STATE RELIABILITY.
- ●RoHS COMPLIANT.

Description

The High Efficiency Red source color devices are made With Gallium Arsenide Phosphide on Gallium Phosphide Orange Light Emitting Diode.

The Green source color devices are made with Gallium Phosphide Green Light Emitting Diode.

Package Dimensions



- 1. All dimensions are in millimeters (inches).
- 2. Tolerance is $\pm 0.25(0.01")$ unless otherwise noted.
- 3. Lead spacing is measured where the leads emerge from the package.
- 4. Specifications are subject to change without notice.

SPEC NO: DSAB9091 **REV NO: V.7** DATE: NOV/22/2005 PAGE: 1 OF 3 **CHECKED: Allen Liu** DRAWN: Y.W.WANG

APPROVED: J. Lu

Kingbright

Selection Guide

| Part No. | Dice | Lens Type | lv (mcd) @ 20mA | | Viewing Angle |
|-----------|---------------------------------|-----------------|--------------------|------|------------------|
| | | | Min. | Тур. | 2 θ1/2 |
| L-115WEGW | HIGH EFFICIENCY RED (GaAsP/GaP) | WHITE DIFFLICED | 10 | 40 | 60° |
| | GREEN (GaP) | WHITE DIFFUSED | 10 | 35 | |

Note:

Electrical / Optical Characteristics at T_A=25°C

| Symbol | Parameter | Device | Тур. | Max. | Units | Test Conditions |
|----------------|--------------------------|------------------------------|------------|------------|-------|---------------------------|
| λpeak | Peak Wavelength | High Efficiency Red Green | 627 565 | | nm | I _F =20mA |
| λD | Dominant Wavelength | High Efficiency Red Green | 625 568 | | nm | I _F =20mA |
| Δλ1/2 | Spectral Line Half-width | High Efficiency Red Green | 45 30 | | nm | I _F =20mA |
| С | Capacitance | High Efficiency Red Green | 15 15 | | pF | V _F =0V;f=1MHz |
| V _F | Forward Voltage | High Efficiency Red Green | 2.0 2.2 | 2.5 2.5 | V | I _F =20mA |
| lR | Reverse Current | High Efficiency Red Green | | 10 10 | uA | VR = 5V |

Absolute Maximum Ratings at TA=25°C

| Parameter | High Efficiency Red | Green | Units | | |
|-------------------------------|---------------------|-------|-------|--|--|
| Power dissipation | 105 | 105 | mW | | |
| DC Forward Current | 30 | 25 | mA | | |
| Peak Forward Current [1] | 160 | 140 | mA | | |
| Reverse Voltage | 5 | 5 | V | | |
| Operating/storage Temperature | -40°C To +85°C | | | | |
| Lead Solder Temperature [2] | 260°C For 3 Seconds | | | | |
| Lead Solder Temperature [3] | 260°C For 5 Seconds | | | | |


Notes:

- 1. 1/10 Duty Cycle, 0.1ms Pulse Width.
- 2. 2mm below package base.
- 3. 5mm below package base.

SPEC NO: DSAB9091 REV NO: V.7 DATE: NOV/22/2005 PAGE: 2 OF 3
APPROVED: J. Lu CHECKED: Allen Liu DRAWN: Y.W.WANG


 $^{1. \}theta 1/2$ is the angle from optical centerline where the luminous intensity is 1/2 the optical centerline value.


Kingbright





High Efficiency Red / Green


L-115WEGW











Remarks:

If special sorting is required (e.g. binning based on forward voltage, luminous intensity/ luminous flux or wavelength), the typical accuracy of the sorting process is as follows:

- 1. Wavelength: +/-1nm
- 2. Luminous Intensity/ Luminous Flux: +/-15%
- 3. Forward Voltage: +/-0.1V

Note: Accuracy may depend on the sorting parameters.

SPEC NO: DSAB9091 REV NO: V.7 DATE: NOV/22/2005 PAGE: 3 OF 3
APPROVED: J. Lu CHECKED: Allen Liu DRAWN: Y.W.WANG