TECHNICAL DATA - XX Series

Electrical

Contact resistance: ≤ 3 m Ohm

Insulation resistance - initial: > 2 G Ohm

- after damp heat test: > 1 G Ohm Dielectric strength: 1500 V dc

Rated current: 16 A AWG: 2.5 mm²/14 AWG

Capacitance between contacts: ≤ 4 pF

Mechanical

Lifetime: >1000 cycles

Insertion / withdrawal force: ≤ 20 N Cable O.D. range: 3.5 mm - 8.0 mm

Materials

Shell: Zinc diecast ZnAl4Cu1, gal Ni over Cu plating Insert: Polyamide PA 6.6 30% GR (glass reinforced)

Contacts: Bronze CuSn6

Contact surface: gal 2 µm Ag silver Latch lock (female): St3K32 Strain-relief clamp: POM

Antikink bushing: PA + PU

Environmental

Temperature range: -30° C to + 80° C

Flammability: UL 94HB

Solderability: complies with IEC 68-2-20

Compatibility:

IEC 61076-2-103 standard & Switchcraft® QG & Cannon XLR