

Miniature cutting insert, type AG HC5640 for inner grooves

ATORN®

Application

For inner grooves in the material groups of steel and (stainless steel) with low to high cutting speeds and medium cutting conditions.

Version

- solid carbide cutting insert with inner cooling

Advantage

- tough cemented carbide type for broad application field
- stable geometry for cutting insert
- ideal for use with inefficient machines and unstable cutting conditions



Art. No.	17129 124
ISO name	AG
Shaft diameter	5 mm
Length	51 mm
Clearance length	15 mm
Programming size 2	1.2 mm
Recessing width	1.5 mm
Programming size	2.3 mm
Min. bore diameter	5.1 mm
Machining direction	Right
Carbide type	HC5640
Material to be processed	Steel, Stainless steel, Non-ferrous metal, Cast metal

EAN-Code

4050293266801