

SVAC clamp holder for lathes, positive

For longitudinal and copy turning using VC indexable inserts

ATORN[®]

Application

For longitudinal and copy turning using VC 35° indexable inserts



Version

- Precision-made steel support, bronzed, hardened, type V, pitch angle 90°, tip angle 35°, clearance angle 7°

Art. no.	17829 089
ISO name	SVAC R/L 1212 X16-A
Shaft height	12 mm
Shank width	12 mm
Length	130 mm
Programming size	12 mm
Suitable for indexable inserts	VC.. 1604..
Tool design	Left
DIN	4983

EAN-Code

4050293693010