

SODIMM3



DDR3 SODIMM

Specifications

- Capacity
 - 2GB, 4GB, 8GB
- Voltage
 - 1.35V
- Storage Temperature
 - -55°C ~ 95°C
- CAS Latency
 - CL11
- Data Rate
 - 1600MHz
- Pin Count
 - 204pin
- Data Width
 - 64Bits
- PCB Height
 - 1.2" (30.50mm)
- Operating Temp. (Standard)
 - 0 ~ 85°C

- Operating Temp. (Wide)
- -40°C ~ 85°C
- Operating Humidity
- 10% ~ 95% (30°C Max. Wet Bulb Temp)
- Warranty
- 10 years

Features

- High performance transfer bandwidth reaches up to 12.8GB/s
- Low voltage of 1.35V for less power consumption
- Original and high quality memory module
- 100% tested for stability, durability, and compatibility
- 30 micro inches Gold Finger Plating (optional)
- Supports operating temperatures from -40°C – 85°C
- Wide Temperature version available by request

Order Information

DDR3 SODIMM

Description	DIMM Type	Capacity	Frequency	CAS Latency	Configuration	RANK(S)	Temp.	P/N
DDR3L	SO-DIMM	2GB	1600	CL11	256Mx16	SR	0~85°C	SP002GISLU160WM0
DDR3L	SO-DIMM	4GB	1600	CL11	512Mx8	SR	0~85°C	SP004GISLU160NM0
DDR3L	SO-DIMM	4GB	1866	CL13	512Mx8	SR	0~85°C	SP004GISLU186NM0
DDR3L	SO-DIMM	8GB	1600	CL11	512Mx8	DR	0~85°C	SP008GISLU160NM0
DDR3L	SO-DIMM	8GB	1866	CL13	512Mx8	DR	-40~85°C	SP008GISLU186NM0