

## Electronic manual hanging scales CH

Up to max. 50 kg

**KERN**

### Application:

For rapid checking of weights with high mobility.

### Execution:

- Large LED display
- Display units: kg/lb/N
- Functions: AUTO OFF
- Pull-out tape measure, length 1 m
- Data hold function (weight display can be frozen for 5 s)
- Tara button for zeroing under load

### Delivery:

With battery



<b>Art. no.</b>	<b>44228 010</b>
<b>Brand</b>	KERN
<b>Manufacturer Part Number</b>	CH 15K20
<b>Type description</b>	CH 15K20
<b>Max. weight measuring range</b>	15 kg
<b>Digit increment, weight</b>	20 g
<b>Height</b>	270 mm
<b>Housing dimensions (LxWxH)</b>	30 x 90 x 176 mm
<b>Weight</b>	0.25 kg
<b>Gross Weight</b>	0.557 kg
<b>Product Group</b>	443

### EAN

4045761027169