



REVISIONS			
LET	DESCRIPTION	BY	DATE

MD-324(2021)R/G/Y




Part Number	Voltage (V)	Emitting color	Peak wave length λP(nm)	Anode(+) Color of the covered dot
MD-324R1(2021)	5 - 6	Red	630	Green
MD-324R2(2021)	12 - 14			Red
MD-324R3(2021)	24 - 28			Black
MD-324G1(2021)	5 - 6	Green	570	Green
MD-324G2(2021)	12 - 14			Red
MD-324G3(2021)	24 - 28			Black
MD-324Y1(2021)	5 - 6	Yellow	590	Green
MD-324Y2(2021)	12 - 14			Red
MD-324Y3(2021)	24 - 28			Black

MD-325(2021)R/G/Y



Part Number	Voltage (V)	Emitting color	Peak wave length λP(nm)	Anode(+) Color of the covered wire	Cathode(-) Color of the covered wire
MD-325R1(2021)	5 - 6	Red	630	Green	Blue
MD-325R2(2021)	12 - 14			Red	
MD-325R3(2021)	24 - 28			Black	
MD-325G1(2021)	5 - 6	Green	570	Green	
MD-325G2(2021)	12 - 14			Red	
MD-325G3(2021)	24 - 28			Black	
MD-325Y1(2021)	5 - 6	Yellow	590	Green	
MD-325Y2(2021)	12 - 14			Red	
MD-325Y3(2021)	24 - 28			Black	

SCALE	UNIT	MATERIAL		
3/1	m.m			
TITLE		DATE		
LED Indicator MD-324/325		210921	 <b>Oshino Lamps Limited</b> SHINAGAWA, TOKYO, JAPAN	
DRAWN	CHECKED	APPROVED	D.W.G. NO.	REV.
T.I	T.H	T.I	100236-2	