

CIRCUIT BREAKER 3VA6 UL FRAME 150 BREAKING CAPACITY CLASS C 100KA @ 480V 3-POLE, LINE PROTECTION ETU860, LSIG, IN=150A OVERLOAD PROTECTION IR=60A ...150A SHORT CIRCUIT PROTECTION ISD=0,6..10X IN, II=1,5..10X IN NEUTRAL PROTECTION OPTIONAL WITH EXT. CT,UPTO 160% GROUND-FAULT-PROTECTION IG=0,2... 1 X IN, TG=0,05-0,8S W/O CONNECTION



| Model                                                                                                                 |                             |
|-----------------------------------------------------------------------------------------------------------------------|-----------------------------|
| Product brand name                                                                                                    | SETRON                      |
| Product designation                                                                                                   | Molded-case circuit breaker |
| Design of the product                                                                                                 | System protection           |
| Design of the load switch / acc. to UL 489 / Heating, Air Conditioning, and Refrigeration circuit breaker (HACR Type) | Yes                         |
| Design of the overcurrent release                                                                                     | ETU860                      |
| Protective function of the overcurrent release                                                                        | LSIG                        |
| Number of poles                                                                                                       | 3                           |

| General technical data                                                                           |        |
|--------------------------------------------------------------------------------------------------|--------|
| Tension assignée d'isolement $U_i$                                                               | 600 V  |
| Max. rated operational voltage $U_e$ with AC 50/60Hz                                             | 600 V  |
| Active power loss / for rated value of the current / at AC / in hot operating state / per device | 29 W   |
| Active power loss / for rated value of the current / at AC / in hot operating state / per pole   | 9.67 W |
| Mechanical service life (switching cycles) / typical                                             | 20 000 |

|                                                                           |                                         |
|---------------------------------------------------------------------------|-----------------------------------------|
| Electrical endurance (switching cycles) / at AC-1 / at 380/415 V 50/60 Hz | 9 000                                   |
| Electrical endurance (switching cycles) / at AC-1 / at 690 V 50/60 Hz     | 5 000                                   |
| Electrical endurance (switching cycles) / at 480 V / at 50/60 Hz          | 9 000                                   |
| Electrical endurance (switching cycles) / at 600 V / at 50/60 Hz          | 9 000                                   |
| Neutral conductors / upgradeable/retrofitable                             | Yes                                     |
| Ground fault monitoring version                                           | Summation current formation L-conductor |
| Product function                                                          |                                         |
| • communication function                                                  | Yes                                     |
| • other measurement function                                              | Yes                                     |

### Electricity

|                                                                   |       |
|-------------------------------------------------------------------|-------|
| Marking / acc. to UL 489 / 100%-rated breaker                     | No    |
| Max. rated operational voltage of the size of the circuit-breaker | 150 A |
| Courant permanent assigné lu                                      | 150 A |
| Operating current                                                 |       |
| • at 40 °C                                                        | 150 A |
| • at 45 °C                                                        | 150 A |
| • at 50 °C                                                        | 150 A |
| • at 55 °C                                                        | 150 A |
| • at 60 °C                                                        | 150 A |
| • at 65 °C                                                        | 150 A |
| • at 70 °C                                                        | 150 A |

### Switching capacity according to IEC 60947

|                                                                        |        |
|------------------------------------------------------------------------|--------|
| Switching capacity class of the circuit breaker                        | C      |
| Maximum short-circuit current breaking capacity (I <sub>cu</sub> )     |        |
| • at 240 V                                                             | 150 kA |
| • at 415 V                                                             | 110 kA |
| • at 690 V                                                             | 2.5 kA |
| Operational short-circuit current breaking capacity (I <sub>cs</sub> ) |        |
| • at 240 V                                                             | 150 kA |
| • at 415 V                                                             | 110 kA |
| • at 690 V                                                             | 2.5 kA |
| Short-circuit current making capacity (I <sub>cm</sub> )               |        |
| • at 240 V                                                             | 330 kA |
| • at 415 V                                                             | 242 kA |
| • at 690 V                                                             | 3.8 kA |

### Switching capacity according to UL 489

|                           |        |
|---------------------------|--------|
| Breaking capacity current |        |
| • at 240 V                | 200 kA |
| • at 480 Y/277 V          | 100 kA |
| • at 480 V                | 100 kA |
| • at 600 Y/347 V          | 35 kA  |
| • at 600 V                | 35 kA  |

#### Adjustable parameters

|                                                                         |         |
|-------------------------------------------------------------------------|---------|
| Adjustable response value current / I <sub>g</sub> min.                 | 60 A    |
| Adjustable response value current / I <sub>g</sub> min.                 | 150 A   |
| Adjustable response value current / I <sub>g</sub> min.                 | 0.5     |
| Adjustable response value current / I <sub>g</sub> min.                 | 20      |
| Adjustable response value current / I <sub>g</sub> min.                 | 90 A    |
| Adjustable response value current / I <sub>g</sub> min.                 | 1 500 A |
| Adjustable response value current / I <sub>g</sub> min.                 | 0.05 s  |
| Adjustable response value current / I <sub>g</sub> min.                 | 0.5 s   |
| Adjustable response value current / I <sub>g</sub> min.                 | 0.05 s  |
| Adjustable response value current / I <sub>g</sub> min.                 | 0.5 s   |
| Adjustable response value current / I <sub>li</sub> min.                | 225 A   |
| Adjustable response value current / I <sub>li</sub> max.                | 1 500 A |
| Ground fault protection can be switched ON/OFF                          | Yes     |
| Ground fault protection / tripping switchable / I <sub>2t</sub> =ON/OFF | Yes     |
| Adjustable response value current / I <sub>g</sub> min.                 | 30 A    |
| Adjustable response value current / I <sub>g</sub> max.                 | 150 A   |
| Adjustable response value current / t <sub>g</sub> min.                 | 0.05 s  |
| Adjustable response value current / I <sub>g</sub> min.                 | 0.8 s   |

#### Mechanical Design

|             |        |
|-------------|--------|
| Height [in] | 7.8 in |
| Height      | 198 mm |
| Width [in]  | 4.1 in |
| Width       | 105 mm |
| Depth [in]  | 3.4 in |
| Depth       | 86 mm  |

#### Connections

|                                                                 |                    |
|-----------------------------------------------------------------|--------------------|
| Arrangement of electrical connectors / for main current circuit | Without connection |
| Type of electrical connection / for main current circuit        | Without            |

#### Auxiliary circuit

|                                                |   |
|------------------------------------------------|---|
| Number of CO contacts / for auxiliary contacts | 0 |
|------------------------------------------------|---|

#### Accessories

|                                            |     |
|--------------------------------------------|-----|
| Product extension / optional / motor drive | Yes |
|--------------------------------------------|-----|

## Environmental conditions

|                                    |        |
|------------------------------------|--------|
| Protection class IP / on the front | IP40   |
| Ambient temperature                |        |
| • during operation / minimum       | -25 °C |
| • during operation / maximum       | 70 °C  |
| • during storage / minimum         | -40 °C |
| • during storage / maximum         | 80 °C  |

## Certificates

|                                                                                        |    |
|----------------------------------------------------------------------------------------|----|
| Equipment marking / acc. to DIN EN 81346-2                                             | Q  |
| Certificate of suitability / as approval for NAVAL (no combat vessels) / Supplement SB | No |

### General Product Approval

### EMC

### Declaration of Conformity



CSA



UL



VDE



RCM



EG-Konf.

### Shipping Approval

other



ABS

[Miscellaneous](#)

## Further information

### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA6115-7KQ31-0AA0>

### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA6115-7KQ31-0AA0>

### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3VA6115-7KQ31-0AA0](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA6115-7KQ31-0AA0)

### CAX-Online-Generator

<http://www.siemens.com/cax>

### Tender specifications

<http://www.siemens.com/specifications>







**last modified:**

09/15/2017