

MULTILAYER TYPE

HIGH CURRENT FERRITE CHIP BEAD



- Impedance Range: 30 to 1300 Ω .
- Operating Temperature Range: -55°C to +125°C.
- Soldering Method: Reflow or Wave Soldering, suitable for lead free soldering.
- Packaging Method: Tape & Reel (per EIA Specifications).
- Storage Temperature: max. 40°C, RH 70%.
- ROHS compliant.



Features


- Combination of high frequency noise suppression with capability of handling high current.
- Current ratings up to 6 Amps with low DCR.

Application Field

- High current DC power lines, Circuits where a Stable ground is unavailable.

Part Number Code

MLB	160808	-	0060	P	N
Series Name	Size Code		Impedance (ex.0010 =10 Ω $\pm$ 25%)	Classification (A, B, and P)	Rated Current
					L= 1000mA Q= 3000mA
					M= 1500mA R= 4000mA
					N= 2000mA U= 5000mA
					P= 2500mA W= 6000mA



Shape and Dimensions

Size code	Size	Length(L)	unit mm Width (W)	Thickness (T)	Electrode Width (E)
0603	160808	1.6 $\pm$ 0.15	0.8 $\pm$ 0.15	0.8 $\pm$ 0.15	0.3 $\pm$ 0.2
0805	201209	2.0 $\pm$ 0.2	1.25 $\pm$ 0.2	0.9 $\pm$ 0.2	0.5 $\pm$ 0.3
1206	311611	3.2 $\pm$ 0.2	1.6 $\pm$ 0.2	1.1 $\pm$ 0.2	0.5 $\pm$ 0.3
1210	322513	3.2 $\pm$ 0.2	2.5 $\pm$ 0.2	1.3 $\pm$ 0.2	0.5 $\pm$ 0.3
1806	451616	4.5 $\pm$ 0.25	1.6 $\pm$ 0.2	1.6 $\pm$ 0.2	0.6 $\pm$ 0.4
1812	453215	4.5 $\pm$ 0.25	3.2 $\pm$ 0.25	1.5 $\pm$ 0.25	0.6 $\pm$ 0.4

KE KITAGAWA

Specifications



P/N with standard rated current	Impedance (Ω) +/- 25%	Test Freq. (MHz)	DCR max. (Ω)	Standard Rated Current (mA)	Rated Current Selection Chart (mA)							
					L	M	N	P	Q	R	U	W
MLB-160808-0030PQ	30	100	0.040	3000	1000	1500	2000	2500	3000			
MLB-160808-0060PQ	60	100	0.040	3000	1000	1500	2000	2500	3000	-	-	-
MLB-160808-0080PQ	80	100	0.040	3000	1000	1500	2000	2500	3000			
MLB-160808-0120PP	120	100	0.070	2500	1000	1500	2000	2500	-	-	-	-
MLB-160808-0220PN	220	100	0.090	2000	1000	1500	2000	-	-	-	-	-
MLB-160808-0300PN	300	100	0.090	2000	1000	1500	2000	-	-	-	-	-
MLB-160808-0450PM	450	100	0.150	1500	1000	1500	-	-	-	-	-	-
MLB-160808-0600PL	600	100	0.200	1000	1000	1500	-	-	-	-	-	-
MLB-201209-0011PW	11	100	0.015	6000	1000	1500	2000	2500	3000	4000	5000	6000
MLB-201209-0031PW	31	100	0.015	6000	1000	1500	2000	2500	3000	4000	5000	6000
MLB-201209-0040PR	40	100	0.030	4000	1000	1500	2000	2500	3000	4000	-	-
MLB-201209-0060PQ	60	100	0.040	3000	1000	1500	2000	2500	3000	-	-	-
MLB-201209-0080PU	80	100	0.020	5000	1000	1500	2000	2500	3000	4000	5000	-
MLB-201209-0090PU	90	100	0.020	5000	1000	1500	2000	2500	3000	4000	5000	-
MLB-201209-0120PU	120	100	0.020	5000	1000	1500	2000	2500	3000	4000	5000	-
MLB-201209-0220PQ	220	100	0.040	3000	1000	1500	2000	2500	3000	-	-	-
MLB-201209-0250PQ	250	100	0.040	3000	1000	1500	2000	2500	3000	-	-	-
MLB-201209-0300PN	300	100	0.090	2000	1000	1500	2000	-	-	-	-	-
MLB-201209-0330PN	330	100	0.090	2000	1000	1500	2000	-	-	-	-	-
MLB-201209-0600PN	600	100	0.090	2000	1000	1500	2000	-	-	-	-	-
MLB-321611-0050PW	50	100	0.015	6000	1000	1500	2000	2500	3000	4000	5000	6000
MLB-321611-0060PQ	60	100	0.040	3000	1000	1500	2000	2500	3000	-	-	-
MLB-321611-0075PQ	75	100	0.040	3000	1000	1500	2000	2500	3000	-	-	-
MLB-321611-0080PR	80	100	0.030	4000	1000	1500	2000	2500	3000	4000	-	-
MLB-321611-0090PQ	90	100	0.040	3000	1000	1500	2000	2500	3000	-	-	-
MLB-321611-0120PW	120	100	0.015	6000	1000	1500	2000	2500	3000	4000	5000	6000
MLB-321611-0150PN	150	100	0.090	2000	1000	1500	2000	-	-	-	-	-
MLB-321611-0500PP	500	100	0.070	2500	1000	1500	2000	2500	-	-	-	-
MLB-321611-0600PP	600	100	0.070	2500	1000	1500	2000	2500	-	-	-	-
MLB-321611-1200PL	1200	100	0.200	1000	1000	-	-	-	-	-	-	-
MLB-322513-0060PM	60	100	0.15	1500	1000	1500	-	-	-	-	-	-
MLB-322513-1000PN	1000	100	0.09	2000	1000	1500	2000	-	-	-	-	-
MLB-451616-0060PW	60	100	0.015	6000	1000	1500	2000	2500	3000	4000	5000	6000
MLB-451616-0080PW	80	100	0.015	6000	1000	1500	2000	2500	3000	4000	5000	6000
MLB-451616-0470PN	470	100	0.09	2000	1000	1500	2000	-	-	-	-	-
MLB-451616-0850PM	850	100	0.15	1500	1000	1500	-	-	-	-	-	-
MLB-453215-0080PW	80	100	0.015	6000	1000	1500	2000	2500	3000	4000	5000	6000
MLB-453215-0120PW	120	100	0.020	6000	1000	1500	2000	2500	3000	4000	5000	6000
MLB-453215-0150PW	150	100	0.015	6000	1000	1500	2000	2500	3000	4000	5000	6000
MLB-453215-0600PQ	600	50	0.040	3000	1000	1500	2000	2500	3000	-	-	-
MLB-453215-0680PQ	680	50	0.040	3000	1000	1500	2000	2500	3000	-	-	-
MLB-453215-1300PQ	1300	60	0.040	3000	1000	1500	2000	2500	3000	-	-	-

3000 Standard rated current
2500 available option



MULTILAYER TYPE

HIGH CURRENT FERRITE CHIP BEAD



MLB-160808-0030PQ





MLB-160808-0060PQ





MLB-160808-0080PQ



MLB-160808-0120PP



MLB-160808-0220PN





KE KITAGAWA



MULTILAYER TYPE

HIGH CURRENT FERRITE CHIP BEAD



MLB-160808-0300PN





MLB-160808-0450PM





MLB-160808-0600PL



MLB-201209-0011PW



MLB-201209-0031PW





KE KITAGAWA



MULTILAYER TYPE

HIGH CURRENT FERRITE CHIP BEAD



MLB-201209-0040PR





MLB-201209-0060PQ





MLB-201209-0080PU



MLB-201209-0090PU



MLB-201209-0120PU





KE KITAGAWA



MULTILAYER TYPE

HIGH CURRENT FERRITE CHIP BEAD



MLB-201209-0220PQ





MLB-201209-0250PQ





MLB-201209-0300PN



MLB-201209-0330PN



MLB-201209-0600PN





KE KITAGAWA



MULTILAYER TYPE

HIGH CURRENT FERRITE CHIP BEAD



MLB-321611-0050PW





MLB-321611-0060PQ





MLB-321611-0075PQ



MLB-321611-0080PR



MLB-321611-0090PQ





KE KITAGAWA



MULTILAYER TYPE

HIGH CURRENT FERRITE CHIP BEAD



MLB-321611-0120PW





MLB-321611-0150PN



MLB-321611-0500PP





MLB-321611-0600PP





MULTILAYER TYPE

HIGH CURRENT FERRITE CHIP BEAD



MLB-321611-1200PL





MLB-322513-0060PM





MLB-322513-1000PN



MLB-451616-0060PW



MLB-451616-0080PW





KE KITAGAWA



MULTILAYER TYPE

HIGH CURRENT FERRITE CHIP BEAD



MLB-451616-0470PN





MLB-451616-0850PM





MLB-453215-0080PW



MLB-453215-0120PW



MLB-453215-0150PW





KE KITAGAWA



MULTILAYER TYPE

HIGH CURRENT FERRITE CHIP BEAD

MLB-453215-0600PQ



MLB-453215-0680PQ



MLB-453215-1300PQ

