

## 5-axis centring vice AZS-100

Mechanical clamping system, mechanical with power transmission

**ATORN**<sup>®</sup>

### Application

For NC machines, machining centres, tool manufacture, mould making, fixture construction and series production.

### Version


- All guidance faces hardened and ground
- Low torque for high clamping force
- Integrated drill holes with 200 mm pitch for ATORN zero point clamping system
- Low-lying spindle for improved accessibility
- Clamping force details on basic body
- Scaling for quick adjustment and orientation guide on basic body

### Advantage

- Extremely stiff for low vibration
- Quick conversion to fixed jaw clamp
- Simple and straightforward to handle, the system can be changed over very quickly.
- Interfering edges optimised in design

### Delivery

1 pc. AZS-100 vice; incl. 1 set of gripper jaws 3.5 mm, 1 pc. short shaft and 4 pcs. Adjustable clamps



<b>Art. No.</b>	<b>28763 010</b>
<b>Jaws width</b>	100 mm
<b>Body height</b>	200 mm
<b>Body length</b>	420 mm
<b>Min./max. clamping width</b>	12-256 mm
<b>Tension force</b>	40 kN
<b>Weight</b>	42 kg

### EAN-Code

4050293715996