

Micrometer

with extra-flat

Mitutoyo

Application:

For measuring hub thickness, bearing bushes, etc.

Execution:

- Semi-gloss chrome-plated scale drum and sleeve
- Carbide-tipped measuring faces
- Friction coupling for consistent, repeatable measuring force

Advantage:

- Accesses hard-to-reach measuring points

Delivery:

Includes box, setting standard



Art. no.	32016 588
Brand	MITUTOYO
Manufacturer Part Number	147-302
Min./max. length measuring range	25-50 mm
Vernier scale	0.01 mm
Measuring surface diameter	6.3 mm
Measuring spindle increments	0.5 mm
Bracket depth	6.5 mm
Spindle clamping	No
Error limit	2 µm
Display	Nonius
Min./max. measurement force	5-10 N
Calibration Group	D
Gross Weight	0.285 kg
Product Group	3MA

EAN

4946368020433